

Features

- Pin-Out Compatible with Lm78xx Linear Regulators
- High Efficiency
- Short Circuit Protection
- Over Temperature Protection
- Lead Free Design, RoHS Compliant
- Designed according to IEC/EN/UL 62368-1

Description

The B78EXX-0R5 Series are non-isolated DC/DC converters suited to replace 0.5 Amp LM78xx linear regulators. Designed with highly efficiency, allow the operating temperature range of these units to be -40°C to +85°C in a 11.6×7.5×10.2mm non-conducted black plastic case. Further features include wide 6~36VDC input voltage range, short circuit protection and over temperature protection.


Models and Ratings

Model Number	Input Voltage Range (VDC)	Output Voltage (VDC)	Output Current (mA)		Efficiency typ. (%)		Capacitive Load max. (μF)
			Min. Load	Full Load	Min. Vin	Max. Vin	
B78E03-0R5	6 - 30 24V nominal	3.3	0	500	90	80	680
B78E05-0R5	7 - 36 24V nominal	5	0	500	94	84	680
B78E6R5-0R5	8 - 36 24V nominal	6.5	0	500	94	84	470
B78E12-0R5	15 - 36 24V nominal	12	0	500	97	92	100
B78E15-0R5	18 - 36 24V nominal	15	0	500	97	94	100



Input Specifications		
Input voltage range		See Models and Ratings table
Input filter		Capacitor Type
Output Specifications		
Output current		0.5 A max.
Voltage accuracy	Nominal Vin	±3% max.
Minimum load		See Models and Ratings table
Line regulation	At full load	±0.5% max.
Load regulation	10% to 100% load	±0.75% max.
Ripple and noise	20MHz bandwidth	85 mVp-p max.
Capacitive load		See Models and Ratings table
Short circuit protection		Continuous, automatic recovery
Temperature coefficient		±0.03% / °C max.
General Specifications		
Efficiency	Nominal Vin and full load	See Models and Ratings table
Switching frequency	PWM	410 kHz typ.
Reliability, calculated MTBF	MIL-HDBK-217F, Ground Benign	1 × 10 ⁶ h
Operating ambient temperature	With derating	-40°C to +85°C
Maximum case temperature		+105°C
Storage temperature range		-55°C to +125°C
Relative humidity		95% RH max.
Over temperature protection	The IC Thermal Shutdown Temperature	+150°C typ.
Physical Specifications		
Case material		Plastic (UL 94 V-0)
Dimensions		11.6 × 7.5 × 10.2 mm
Weight		1.6 g typ.

Characteristic Curves

Power Derating Curve



Mechanical




Pinout	
PIN	Function
1	+Vin
2	GND
3	+Vout

Dimensions in mm
Tolerances: xx.x ±0.5
 x.xx ±0.25
Pins: ±0.10

Design and feature configurations


EMI Filter

Input filter components are used to meet emissions requirement for the module. These components should be mounted as close as possible to the module; and all leads should be minimized to decrease EMI noise.




EN55032 Class B							
Models	MOV	L1	C0	C01	L2	C1	C2
B78EXX-0R5	20D470K	300μH	470μF/50V	4.7μF/50V MLCC	5mH CMC	10μF/50V MLCC	22μF/25V MLCC

Typical Application




C1=10μF/50V MLCC, C2 =22μF/25V MLCC

Wave Soldering Temperature Curve



Carton Package



TUBE = 42PCS
 INNER CARTON = 50 TUBE = 50*42 = 2100PCS
 EXPORT CARTON = 2 INNER CARTON = 2*2100 = 4200PCS

For More Information:

Americas-prodinfo@pulseelectronics.com | Europe-comms@pulseelectronics.com | Asia-prodinfo@pulseelectronics.com

Performance warranty of products offered on this datasheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners. © Copyright, 2023. Pulse Electronics, Inc. All rights reserved.