

# Power Inductor

## BPSD Series



### Overview

Power inductors are passive electronic components used in various circuits to store energy in a magnetic field when electrical current flows through them. They are critical in filtering, energy storage, and noise suppression in power electronic systems. They are designed to handle higher currents and are optimized for minimal power loss and thermal efficiency.

### Benefits

1. Ferrite SMD Shielded Type
2. Unshielded power inductor
3. Various package size and wide inductance range

### Applications

1. Graphic cards
2. DC/DC converters

### Product Information


Series	L (mm)	W(mm)	T (mm)	Inductance (μH)
BPSD	3.3	3.0	1.5	0.15 ~ 8200
	3.3	3.0	2.1	
	4.5	4.0	3.2	
	5.8	5.2	2.5	
	5.8	5.2	3.0	
	5.8	5.2	4.5	
	7.8	7.0	3.5	
	7.8	7.0	5.0	
	10	9.0	4.0	
	10	9.0	5.4	
	10	9.0	6.5	





## BPSD00100965 Series Specification

### 6 Configuration and Dimensions:



Dimensions in mm

TYPE	100965
A	10.0±0.4
B	9.0±0.4
C	6.5±0.4
D	3.5

### Net Weight (grms)

SIZE CODE	Net Weight (grms)
100965	2.08(Typ.)

### 7 Electrical Characteristics:

Part No.	Inductance (uH)	Test Freq.	RDC (Ω)Max.	Isat (A)	Irms (A)	Tolerance (±%)	Marking
BPSD00100965220□00	22	2.52 MHz, 1 V	0.08	3.8	3.8	10,20	220
BPSD00100965471□00	470	1 kHz, 1 V	1.421	0.82	0.82	10,20	471
BPSD00100965102□00	1000	1 kHz, 1 V	2.9	0.6	0.6	10,20	102
BPSD00100965122□00	1200	1 kHz, 1 V	3.5	0.5	0.5	10,20	122
BPSD00100965152□00	1500	1 kHz, 1 V	3.8	0.6	0.6	10,20	152
BPSD00100965202□00	2000	1 kHz, 1 V	6.6	0.4	0.4	10,20	202
BPSD00100965222□00	2200	1 kHz, 1 V	6	0.4	0.4	10,20	222
BPSD00100965602□00	6000	1 kHz, 1 V	14	0.27	0.27	10,20	602
BPSD00100965822□00	8200	1 kHz, 1 V	50	0.2	0.2	10,20	822


**NOTE:** □-tolerance K=±10% / M=±20%

1. Operating temperature range - 40 °C ~ 125 °C (Including self - temperature rise)
2. Isat for Inductance drop 10% from its value without current.
3. I rms for a 40 °C temperature rise from 25 °C ambient.

## BPSD00100965 Series Specification

### 8 BPSD00100965 Series

#### 8.1 Construction:



#### 8.2 Material List:

No	Part	Material
1	CORE	FERRITE
2	WIRE	MAGNET WIRE
3	TERMINAL	Ag/Ni/Sn

## BPSD00100965 Series Specification

### 9 Reliability Of Ferrite Wire Wound Power Inductor

#### 1-1.Mechanical Performance


No	Item	Specification	Test Method
1-1-1	Vibration	Appearance: No damage Inductance: within $\pm 10\%$ of initial value	Test device shall be soldered on the substrate Oscillation Frequency: 10 to 55 to 10Hz for 1min Amplitude: 1.5mm Time: 2hrs for each axis (X, Y & Z), total 6hrs
1-1-2	Resistance to Soldering Heat	Appearance: No damage	Pre-heating: 150°C, 1min Solder Composition: Sn/Ag3.0/Cu0.5 Solder Temperature: 260 $\pm$ 5°C Immersion Time: 10 $\pm$ 1sec
1-1-3	Solder ability	The electrodes shall be at least 95% covered with new solder coating	Pre-heating: 150°C, 1min Solder Composition: Sn/Ag3.0/Cu0.5 Solder Temperature: 245 $\pm$ 5°C Immersion Time: 4 $\pm$ 1sec
1-1-4	Resistance to solvent	There must be no change in appearance or obliteration of marking.	Inductors must withstand 6 minutes of alcohol or water.

#### 1-2.Environmental Performance

No	Item	Specification	Test Method															
1-2-1	Temperature Shock	Appearance: No damage Inductance: within $\pm 10\%$ of initial value	10 cycles (Air to Air) 1 cycles shall consist of: 30 minutes exposure to -55 °C 30 minutes exposure to 125 °C 15 seconds maximum transition between temperatures															
1-2-2	Temperature Cycle		One cycle: <table border="1"> <thead> <tr> <th>Step</th> <th>Temperature (°C)</th> <th>Time (min)</th> </tr> </thead> <tbody> <tr> <td>1</td> <td>-40<math>\pm</math>3</td> <td>30</td> </tr> <tr> <td>2</td> <td>25<math>\pm</math>2</td> <td>3</td> </tr> <tr> <td>3</td> <td>125<math>\pm</math>3</td> <td>30</td> </tr> <tr> <td>4</td> <td>25<math>\pm</math>2</td> <td>3</td> </tr> </tbody> </table>	Step	Temperature (°C)	Time (min)	1	-40 $\pm$ 3	30	2	25 $\pm$ 2	3	3	125 $\pm$ 3	30	4	25 $\pm$ 2	3
Step	Temperature (°C)	Time (min)																
1	-40 $\pm$ 3	30																
2	25 $\pm$ 2	3																
3	125 $\pm$ 3	30																
4	25 $\pm$ 2	3																
1-2-3	Humidity Resistance		Total: 100cycles Measured after exposure in the room condition for 24hrs Temperature: 40 $\pm$ 2°C Relative Humidity: 90 ~ 95% Time: 1000hrs Measured after exposure in the room condition for 24hrs															
1-2-4	Heat Life		Temperature: 85 $\pm$ 3°C Applied Current: Rated Current Time: 1000hrs Measured after exposure in the room condition for 24hrs															
1-2-5	Cold Resistance		Temperature: -40 $\pm$ 3°C Time: 1000hrs Measured after exposure in the room condition for 24hrs															

## BPSD00100965 Series Specification

### Reflow Soldering Profile



Lead-Free(LF)標準溫度分析範圍

Refer to J-STD-020C


管制項目 Item.	升溫區 Ramp-up	預熱區 Pre-heating	迴焊區 Reflow	Peak Temp	冷卻區 Cooling
溫度範圍 Temp.scope	R.T ~ 150°C	150°C ~ 200°C	217°C	260±5°C	Peak Temp.~150°C
標準時間 Time spec.	-	60 ~ 180 sec	60 ~ 150 sec	20 ~ 40 sec	-
實際時間 Time result	-	75 ~ 100 sec	90 ~ 120 sec	20 ~ 35 sec	-

## BPSD00100965 Series Specification

### 10 Packaging:

#### 10.1 Packaging -Cover Tape


The force for tearing off cover tape is 10 to 130 grams in the arrow direction.



#### 10.2 Packaging Quantity

TYPE	PCS/REEL
100965	500

#### 10.3 Reel Dimensions





Dimensions in mm

TYPE	A	B	C	D
100965	330	100	13	24.4

## BPSD00100965 Series Specification


### 10 Packaging:

#### 10.4 Tape Dimensions in mm



TYPE	K0	D	E	W	P	P0	P2
100965	7	1.55	1.75	24	16	4	2

### 11 Recommended Land Pattern:



Dimensions in mm

TYPE	A	B
100965	11	4.0



### 12 Note:

1. Please make sure that your product has been evaluated and confirmed against your specifications when our product is mounted to your product.
2. Do not knock nor drop.
3. All the items and parameters in this product specification have been prescribed on the premise that our product is used for the purpose, under the condition and in the environment agreed upon between you and us. You are requested not to use our product deviating from such agreement.
4. Please keep the distance between transformer/coil and other components (refer to the standard IEC 950)
5. The moisture sensitivity level (MSL) of products is classified as level 1.



# BPSD00100965 Series Specification

**13** Graph:



BPSD00100965220□00





BPSD00100965471□00



BPSD00100965102□00





BPSD00100965122□00





# BPSD00100965 Series Specification

## 13 Graph:

BPSD00100965202□00



BPSD00100965602□00



BPSD00100965822□00

