


# Dual 1Gigabit Slimline Magnetic Modules

HX5020HL, HX6135HL, and HX6136HL



- Fully RoHS and Halogen Free
- Designed to exceed IEEE802.3au over Industrial temperature range -40 to +85°C
- Up to 35W PoE over 100m of UTP using 4pair connection
- Compatible with all Major PHYs
- 30% PCB saving compared to standard dual port devices

Electrical Specifications @ 25°C - Operating Temperature -40°C to 85°C

| Part Number | Inductance  | Turns Ratio | Isolation (Pri:Sec) | Power over Ethernet (PoE) |                              |
|-------------|-------------|-------------|---------------------|---------------------------|------------------------------|
|             |             |             |                     | DC Current (@ 70°C)       | Power Supported (4 pair UTP) |
| HX5020HL    | 350uH @ 8mA | 1.00 +/- 2% | 1500Vrms / 60sec    | 350mA                     | 35W (PSE)                    |
| HX6135HL    | 350uH @ 8mA | 1.00 +/- 2% | 1500Vrms / 60sec    | 350mA                     | 35W (PSE)                    |
| HX6136HL    | 350uH @ 8mA | 1.00 +/- 2% | 1500Vrms / 60sec    | 350mA                     | 35W (PSE)                    |

| Part Number | Insertion Loss |          |        | Return Loss |          |        | CMRR  |           |        |
|-------------|----------------|----------|--------|-------------|----------|--------|-------|-----------|--------|
|             | 100kHz         | 1-100MHz | 125MHz | 1-40MHz     | 60-80MHz | 100MHz | 2MHz  | 30-100MHz | 200MHz |
| HX5020HL    | -1.2dB         | -1.5dB   | -2.0dB | -16dB       | -10dB    | -8dB   | -50dB | -20dB     | -15dB  |
| HX6135HL    | -1.2dB         | -0.5dB   | -1.0dB | -18dB       | -13dB    | -11dB  | -50dB | -35dB     | -30dB  |
| HX6136HL    | -1.2dB         | -0.5dB   | -1.0dB | -18dB       | -13dB    | -11dB  | -50dB | -20dB     | -15dB  |

## Notes:

1. Storage Temperature: -50°C to 125°C

Compliance to J-STD:

A. J-STD-002: Solderability at 245°C Reflow Profile

B. J-STD-020: Moisture Sensitive Level 1

C. J-STD-075: R7, 245°C Maximum Through Reflow Solder

2. The HL suffix part is supplied in tubes with 15pcs/tube. To order tape and reel packaging add a 'T' suffix to the part number (ie: HX6135HL becomes HX6135HLT).

Where quantity per 13" reel will be 250pcs - see page 3 for more details.

3. Header: DAP (Diallyl Phthalate) with flammability Rating UL 94V-0 or better

4. Lead Frame: Cooper Alloy

Under plated: Half Hard Ductile Nickel 50-100" (1.3-2.5um)

Over plated : 100% Tin electro-deposited per ASTM B545 300 - 50u"(8-13um)

Finish : Matte finish 100% Tin solder


# Dual 1Gigabit Slimline Magnetic Modules

HX5020HL, HX6135HL, and HX6136HL




## Mechanical

HXxxxxHL




## Schematics

HX5020HL



HX6136HL




# Dual 1Gigabit Slimline Magnetic Modules

HX5020HL, HX6135HL, and HX6136HL



## Schematic

### HX6135HL



## Tape & Reel

### HX5020HL, HX6135HL and HX6136HL



|                |            |                |                     |                |            |                |            |
|----------------|------------|----------------|---------------------|----------------|------------|----------------|------------|
| W              | 44.00±0.30 | P              | 24.00±0.10          | A <sub>0</sub> | 11.50±0.10 | B <sub>0</sub> | 27.85±0.10 |
| S <sub>0</sub> | 40.40±0.10 | P <sub>0</sub> | 4.00±0.10           | A <sub>1</sub> | -----      | B <sub>1</sub> | -----      |
| E              | 1.75±0.10  | P <sub>2</sub> | 2.00±0.15           | A <sub>2</sub> | -----      | B <sub>2</sub> | -----      |
| F              | 20.20±0.15 | D <sub>0</sub> | -----               | K <sub>0</sub> | 9.25±0.10  | K <sub>1</sub> | 8.50±0.10  |
| T              | 0.50±0.05  | D <sub>1</sub> | 1.50 ±0.10<br>-0.00 |                |            |                | UNIT: mm   |

ALL Dimensions meet EIA-481-D requirements.

1. **Material:** Black Conductive Polystyrene
2. **Components per Reel:** 250 pcs
3. **Quantity per box:** 5x reels = 1250 pcs

## For More Information:

Americas - [prodinfinetworkamericas@yageo.com](mailto:prodinfinetworkamericas@yageo.com) | Europe - [prodinfinetworkemea@yageo.com](mailto:prodinfinetworkemea@yageo.com) | Asia - [prodinfinetworkapac@yageo.com](mailto:prodinfinetworkapac@yageo.com)

Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners. © Copyright, 2022. Pulse Electronics, Inc. All rights reserved.