

Features

- 7pin SIP Package
- Input / Output Isolation: 6400VDC or 8000VDC
- High Efficiency
- Operating Temperature: -40°C to +85°C
- Lead Free Design, RoHS Compliant
- Designed according to IEC/EN/UL 62368-1

Applications

These converters are well suitable for battery operated equipment, measurement equipment, telecom, wireless network, Industry control system, everywhere where isolated, tightly regulated voltages and compact size are required.

Models and Ratings								
Model Number HBA1H6 HBA1H8	Input Voltage Range (VDC)	Output Voltage (VDC)	Output Current (mA)		Input Current (mA) typ.		Efficiency (%) typ.	Capacitive Load (μF) max.
			Full Load	No Load	No Load	Full Load		
HBA1-05S0H6 HBA1-05S0H8	4.5 - 5.5 5V nominal	3.3	303	55	278	76	3300	
HBA1-05S1H6 HBA1-05S1H8		5	200	55	271	78	2200	
HBA1-05SBH6 HBA1-05SBH8		7.2	140	55	273	78	1000	
HBA1-05SAH6 HBA1-05SAH8		9	111	55	263	80	1000	
HBA1-05S2H6 HBA1-05S2H8		12	84	55	265	80	470	
HBA1-05S3H6 HBA1-05S3H8		15	66	55	253	82	470	
HBA1-05D0H6 HBA1-05D0H8		±3.3	±151	55	281	75	2200 / 2200	
HBA1-05D1H6 HBA1-05D1H8		±5	±100	55	271	78	1000 / 1000	
HBA1-05DBH6 HBA1-05DBH8		±7.2	±70	55	273	78	470 / 470	
HBA1-05DAH6 HBA1-05DAH8		±9	±55	55	264	79	470 / 470	
HBA1-05D2H6 HBA1-05D2H8		±12	±41	55	263	79	220 / 220	
HBA1-05D3H6 HBA1-05D3H8		±15	±33	55	258	81	220 / 220	

Models and Ratings (continued)								
Model Number HBA1H6 HBA1H8	Input Voltage Range (VDC)	Output Voltage (VDC)	Output Current (mA)		Input Current (mA) typ.		Efficiency (%) typ.	Capacitive Load (μ F) max.
			Full Load	No Load	No Load	Full Load		
HBA1-12S0H6 HBA1-12S0H8	10.8 - 13.2 12V nominal	3.3	303	30	116	76	3300	
HBA1-12S1H6 HBA1-12S1H8		5	200	30	113	78	2200	
HBA1-12SBH6 HBA1-12SBH8		7.2	140	30	114	78	1000	
HBA1-12SAH6 HBA1-12SAH8		9	111	30	110	80	1000	
HBA1-12S2H6 HBA1-12S2H8		12	84	30	110	81	470	
HBA1-12S3H6 HBA1-12S3H8		15	66	30	106	82	470	
HBA1-12D0H6 HBA1-12D0H8		\pm 3.3	\pm 151	30	117	75	2200 / 2200	
HBA1-12D1H6 HBA1-12D1H8		\pm 5	\pm 100	30	113	78	1000 / 1000	
HBA1-12DBH6 HBA1-12DBH8		\pm 7.2	\pm 70	30	114	78	470 / 470	
HBA1-12DAH6 HBA1-12DAH8		\pm 9	\pm 55	30	110	79	470 / 470	
HBA1-12D2H6 HBA1-12D2H8		\pm 12	\pm 41	30	108	80	220 / 220	
HBA1-12D3H6 HBA1-12D3H8		\pm 15	\pm 33	30	108	81	220 / 220	
HBA1-15S0H6 HBA1-15S0H8		13.5 - 16.5 15V nominal	3.3	303	25	93	76	3300
HBA1-15S1H6 HBA1-15S1H8			5	200	25	91	78	2200
HBA1-15SBH6 HBA1-15SBH8	7.2		140	25	91	78	1000	
HBA1-15SAH6 HBA1-15SAH8	9		111	25	88	80	1000	
HBA1-15S2H6 HBA1-15S2H8	12		84	25	88	81	470	
HBA1-15S3H6 HBA1-15S3H8	15		66	25	85	82	470	

Models and Ratings (continued)								
Model Number HBA1H6 HBA1H8	Input Voltage Range (VDC)	Output Voltage (VDC)	Output Current (mA)		Input Current (mA) typ.		Efficiency (%) typ.	Capacitive Load (μ F) max.
			Full Load		No Load	Full Load		
HBA1-15D0H6 HBA1-15D0H8	13.5 - 16.5 15V nominal	\pm 3.3	\pm 151		25	94	75	2200 / 2200
HBA1-15D1H6 HBA1-15D1H8		\pm 5	\pm 100		25	91	78	1000 / 1000
HBA1-15DBH6 HBA1-15DBH8		\pm 7.2	\pm 70		25	91	78	470 / 470
HBA1-15DAH6 HBA1-15DAH8		\pm 9	\pm 55		25	88	79	470 / 470
HBA1-15D2H6 HBA1-15D2H8		\pm 12	\pm 41		25	87	80	220 / 220
HBA1-15D3H6 HBA1-15D3H8		\pm 15	\pm 33		25	86	81	220 / 220
HBA1-24S0H6 HBA1-24S0H8	21.6 - 26.4 24V nominal	3.3	303		20	58	76	3300
HBA1-24S1H6 HBA1-24S1H8		5	200		20	57	78	2200
HBA1-24SBH6 HBA1-24SBH8		7.2	140		20	57	78	1000
HBA1-24SAH6 HBA1-24SAH8		9	111		20	55	80	1000
HBA1-24S2H6 HBA1-24S2H8		12	84		20	55	81	470
HBA1-24S3H6 HBA1-24S3H8		15	66		20	56	78	470
HBA1-24D0H6 HBA1-24D0H8		\pm 3.3	\pm 151		20	59	75	2200 / 2200
HBA1-24D1H6 HBA1-24D1H8		\pm 5	\pm 100		20	57	78	1000 / 1000
HBA1-24DBH6 HBA1-24DBH8		\pm 7.2	\pm 70		20	57	78	470 / 470
HBA1-24DAH6 HBA1-24DAH8		\pm 9	\pm 55		20	55	79	470 / 470
HBA1-24D2H6 HBA1-24D2H8		\pm 12	\pm 41		20	54	80	220 / 220
HBA1-24D3H6 HBA1-24D3H8		\pm 15	\pm 33		20	56	78	220 / 220

Input Specifications

Input voltage	See Models and Ratings table	
Input filter	Capacitor	

Output Specifications

Output power	1 Watts max.	
Voltage accuracy	Nominal Vin and full load	±5% max.
Minimum load	10% load of full load	
Line regulation	1% Vin step	±1.5% max.
Load regulation	10% to 100% load	
	3.3Vout, 5Vout, ±3.3Vout and ±5Vout models	15% max.
	Other models	10% max.
Ripple and noise	20MHz bandwidth and full load	150 mVp-p max.
Capacitive load	Nominal Vin and constant resistive load	See Models and Ratings table
Short circuit protection	1 s max.	
Temperature coefficient	Full Load	±0.03%/°C typ.

General Specifications

Efficiency	Nominal Vin and full load	See Models and Ratings table
Switching frequency	Nominal Vin and full load	80 - 350 kHz
Isolation voltage	Input to output, 1 s	
	Suffix " H6 "	6400 VDC min.
	Suffix " H8 "	8000 VDC min.
Isolation resistance	500 VDC	10 GΩ min.
Isolation capacitance	10 pF max.	
Reliability, calculated MTBF	MIL-HDBK-217F, Ground Benign	2 × 10 ⁶ h
Operating ambient temperature	With derating	-40°C to +105°C
Case temperature	+105°C max.	
Storage temperature range	-55°C to +125°C	
Relative humidity	95% RH max.	
Cooling	Natural convection	


Physical Specifications

Case material	Plastic (UL 94 V-0)	
Pin material	Copper alloy	
Pin Foundation Plating	Nickel	
Pin Surface Plating	Tin	


Potting material	Epoxy (UL 94 V-0)
Dimensions	0.77 × 0.50 × 0.39 inch
	19.5 × 12.5 × 9.8 mm
Weight	4.3 g typ.

Characteristic Curves


Power Derating Curve




Carton Package



TUBE



INNER CARTON: 388*158.5*115



EXPORT CARTON: 405*334*263

TUBE = 15PCS

INNER CARTON = 36 TUBE = 36*15 = 540PCS

EXPORT CARTON = 4 INNER CARTON = 4*540 = 2160PCS

For More Information:

Americas-prodinfo@pulseelectronics.com | Europe-comms@pulseelectronics.com | Asia-prodinfo@pulseelectronics.com

Performance warranty of products offered on this datasheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners. © Copyright, 2023. Pulse Electronics, Inc. All rights reserved.