

# DATA SHEET

## MOLDED RESISTORS

High Power, TO-220, TO-247  
NPM Series  
 $\pm 0.5\%$ ,  $\pm 1\%$ ,  $\pm 5\%$   
30W to 100W  
RoHS compliant & Halogen Free



**YAGEO**

Product specification – September 2, 2025 V.6





## ORDERING INFORMATION

Part number of the high power, molded resistor is identified by the series, power rating, tolerance, packing, temperature coefficient and resistance value.

### PART NUMBER

**NPM**    **35A**    **F**    **T**    **F**    **100R**  
 (1)        (2)        (3)        (4)        (5)        (6)

#### (1) SERIES NAME

NPM Series

### APPLICATIONS

- RF Power Amplifier, snubber circuit
- Switching mode power supply
- Automation control equipment
- Industrial power equipment
- UPS, voltage regulator
- Low power impulse loading

### FEATURES

- Power rating up to 100W @ 25°C while heatsink mounted
- TO-220 molded type for NPM30A/NPM35A/NPM50A/ NPM50V
- TO-247 molded type for NPM10B
- Molded case provides protection and easily to mount.
- Non- inductive design
- RoHS compliant & halogen free

#### (2) POWER RATING

30A = 30W	50V = 50W
35A = 35W	10B= 100W
50A = 50W	

#### (3) TOLERANCE

D = $\pm 0.5\%$	J = $\pm 5\%$
F = $\pm 1\%$	

#### (4) PACKAGING

T = Box Pack

#### (5) TEMPERATURE COEFFICIENT OF RESISTANCE


E= $\pm 50\text{ppm}/^\circ\text{C}$	- = Based on spec
F= $\pm 100\text{ppm}/^\circ\text{C}$	

#### (6) RESISTANCE VALUE


E24 & E96 & E192 Series	
Example:	
10R = 10Ω, 100R= 100Ω, 10K = 10,000Ω	

**DIMENSIONS**


NPM30A




NPM35A




NPM50A



NPM10B



NPM50V



TYPE	DIMENSIONS											Unit: mm	
	W $\pm$ 0.5	H $\pm$ 0.5	H1 $\pm$ 0.5	B $\pm$ 1.5	B1 $\pm$ 1.0	D $\pm$ 0.3	D1 $\pm$ 0.2	$\psi$ d $\pm$ 0.3	C $\pm$ 0.3	T $\pm$ 0.5	P $\pm$ 0.15	P1 $\pm$ 0.3	
NPM30A	10.41	16.26	3.18	12.7	3.3	1.27	0.76	3.18	5.08	3.18	0.5	1.78	
NPM50A	10.41	16.26	-	12.7	3.3	1.27	0.76	-	5.08	3.18	0.5	1.78	


TYPE	DIMENSIONS											Unit: mm	
	W $\pm$ 0.5	H $\pm$ 0.5	H1 $\pm$ 0.5	B $\pm$ 0.5	B1 $\pm$ 0.5	D $\pm$ 0.3	D1 $\pm$ 0.2	$\psi$ d $\pm$ 0.3	C $\pm$ 0.3	T $\pm$ 0.5	P $\pm$ 0.15	P1 $\pm$ 0.3	
NPM10B	15.49	20.44	5.07	14.0	12.03	3.63	1.42	3.63	10.1	4.69	0.55	2.15	

TYPE	DIMENSIONS											Unit: mm		
	W $\pm$ 0.5	H $\pm$ 0.5	H1 $\pm$ 0.5	B $\pm$ 1.0	B1	D $\pm$ 0.3	D1 $\pm$ 0.2	$\psi$ d $\pm$ 0.35	C $\pm$ 0.3	T $\pm$ 0.5	T1 $\pm$ 0.1	H2 $\pm$ 0.5	P $\pm$ 0.2	P1 $\pm$ 0.3
NPM35A	10.16	15.23	2.9	13.5	4 Max	1.26	0.78	3.83	5.08	4.6	1.3	6.25	0.51	2.27


TYPE	DIMENSIONS											Unit: mm	
	W $\pm$ 0.5	H $\pm$ 0.5	H1 $\pm$ 0.5	B $\pm$ 1.5	B1 $\pm$ 1.0	D $\pm$ 0.3	D1 $\pm$ 0.2	$\psi$ d $\pm$ 0.3	C $\pm$ 0.3	T $\pm$ 0.5	P $\pm$ 0.15	P1 $\pm$ 0.3	
NPM50V	10.41	16.26	3.18	12.7	3.3	1.27	0.86	3.18	5.08	3.18	0.55	1.78	

## DERATING CURVE

NPM30W~50W



NPM100W



ELECTRICAL CHARACTERISTICS

CHARACTERISTICS	NPM30A	NPM35A	NPM50A	NPM50V	NPM10B
Power Rating at 25°C on heat sink	30W	35W	50W	50W	100W
Power Rating at 25°C without heat sink	2.25W	2.5W	3W	3W	3.5W
Maximum Working Voltage	350V	350V	350V	420V	350V
Thermal Resistance	4.17°C/W	3.7°C/W	3°C/W	3.7°C/W	1.5°C/W
Voltage Proof on Insulation	1800Vrms				
Inductance	≤0.1μH				
Operating Temp. Range	-65°C to +150°C			-55°C to +150°C	-65°C to +175°C
Temperature Coefficient	±50ppm/°C, ±100ppm/°C, ±200ppm/°C, ±300ppm/°C				

Note: For resistance value out of above range is by request.

RESISTANCE RANGE AND TEMPERATURE COEFFICIENT

Series	Resistance range		T.C.R (ppm/°C)
	±1%	±5%	
NPM	-0.1Ω~1Ω	0.1Ω~1Ω	No Specified
	>1Ω~3Ω	>1Ω~3Ω	±300
	>3Ω~10Ω	>3Ω~10Ω	±100, ±200
	>10Ω~10KΩ	>10Ω~10KΩ	±50, ±100, ±200

Series	Resistance range			T.C.R (ppm/°C)
	±0.5%	±1%	±5%	
NPM50V	-	-	0.05Ω~1Ω	No Specified
	-	>1Ω~3Ω	>1Ω~3Ω	±300
	-	>3Ω~10Ω	>3Ω~10Ω	±100, ±200
	>10Ω~10KΩ	>10Ω~10KΩ	>10Ω~10KΩ	±50, ±100, ±200

**TEST AND REQUIREMENTS**

TEST	TEST METHOD	PROCEDURE	APPRAISE
Short Time Overload	IEC 60115-1 4.13	2 times of the rated power not to exceed 1.5 times maximum continuous. working voltage for 5 seconds.	±0.5%
Voltage Proof on Insulation	IEC 60115-1 4.7	In V-Block for 60 sec. test voltage as above table	No Breakdown
Temperature Coefficient	IEC 60115-1 4.8	Between -55°C to +155°C	By Type
Insulation Resistance	IEC 60115-1 4.6	In V-Block for 60 sec.	>10,000MΩ
Solderability	IEC 60115-1 4.17	245±5°C for 3±0.5 Sec.	95% Min. coverage
Solvent Resistance of Marking	IEC 60115-1 4.30	IPA for 5±0.5 Min. with ultrasonic	No deterioration of coatings and markings
Robustness of Terminations	IEC 60115-1 4.16	Direct load for 10 Sec. the load of weight is 2.4N	±0.2%
Damp Heat Steady State	IEC 60115-1 4.24	40±2°C, 90-95% RH at RCWV(or Umax., whichever less) for 1,000 Hr.(1.5 Hr.on,0.5 Hr. off)	±0.5%
Endurance at 25°C	IEC 60115-1 4.25	25±2°C at RCWV(or Umax., whichever less) for 1,000 Hr.(1.5 Hr.on,0.5 Hr. off)	±1.0%
Temperature Cycling	IEC 60115-1 4.19	→ -65°C → Room Temp. → +150°C Room Temp.(5 cycles)	±0.5%
Resistance to Soldering Heat	IEC 60115-1 4.18	260±3°C for 10±1 Sec., immersed to a point 3±0.5mm from the body	±1.0%

Note:

**RCWV (Rated Continuous Working Voltage):**

The DC or AC (rms) continuous working voltage corresponding to the rated power is determined by the following formula:

$$V = \sqrt{P \times R}$$


or max. working voltage whichever is less

Where

V=Continuous rated DC or  
AC (rms) working voltage (V)


P=Rated power (W)

R=Resistance value (Ω)

**TAPE SPECIFICATION**

Unit: mm

Normal	L	W	H	Qty per Tube (Max.)
NPM30A	529	32.6	7.2	50
NPM35A	529	32.6	7.2	50
NPM50A	529	32.6	7.2	50
NPM50V	529	32.6	7.2	50
NPM10B	590	45.5	8.5	35

**TAPE ON BOX PACKING**

TYPE	DIMENSIONS			Unit: mm/piece
Normal	A	B	C	Quantity Per Box (Max.)
NPM30A	80	90	540	1,000
NPM35A	80	90	540	1,000
NPM50A	80	90	540	1,000
NPM50V	80	90	540	1,000
NPM10B	100	95	600	700

**MARKING****Example:**

YAGEO	= Brand
302	= Date code
35W	= Power rating
0R33	= Resistance
F	= Tolerance

**REVISION HISTORY**

REVISION	DATE	CHANGE NOTIFICATION	DESCRIPTION
Version 6	Sep.02, 2025	-	- Updated the dimensions B and C of the NPM10B series
Version 5	Feb.07, 2025	-	- Revised TO-247 molded type for NPM10B
Version 4	May.06, 2024	-	- Increase thermal resistance and update the derating curve
Version 3	Dec.07, 2023	-	- NPM50V type is included.
Version 2	Sep.6, 2023	-	- Updated legal disclaimer and footer versions numbers
Version 1	May 16, 2022	-	- Deleted NPM20A type.
Version 0	Aug.2, 2021	-	- First issue of this specification

*"Yageo reserves all the rights for revising the content of this datasheet without further notification, as long as the products itself are unchanged. Any product change will be announced by PCN."*

## LEGAL DISCLAIMER

YAGEO, its distributors and agents (collectively, "YAGEO"), hereby disclaims any and all liabilities for any errors, inaccuracies or incompleteness contained in any product related information, including but not limited to product specifications, datasheets, pictures and/or graphics. YAGEO may make changes, modifications and/or improvements to product related information at any time and without notice.

YAGEO makes no representation, warranty, and/or guarantee about the fitness of its products for any particular purpose or the continuing production of any of its products. To the maximum extent permitted by law, YAGEO disclaims (i) any and all liability arising out of the application or use of any YAGEO product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for a particular purpose, non -infringement and merchantability.

YAGEO products are designed for general purpose applications under normal operation and usage conditions. Please contact YAGEO for the applications listed below which require especially high reliability for the prevention of defects which might directly cause damage to the third party's life, body or property: Aerospace equipment (artificial satellite, rocket, etc.), Atomic energy-related equipment, Aviation equipment, Disaster prevention equipment, crime prevention equipment, Electric heating apparatus, burning equipment, Highly public information network equipment, data-processing equipment, Medical devices, Military equipment, Power generation control equipment, Safety equipment, Traffic signal equipment, Transportation equipment and Undersea equipment, or for any other application or use in which the failure of YAGEO products could result in personal injury or death, or serious property damage. Particularly **YAGEO Corporation and its affiliates do not recommend the use of commercial or automotive grade products for high reliability applications or manned space flight.**

Information provided here is intended to indicate product specifications only. YAGEO reserves all the rights for revising this content without further notification, as long as products are unchanged. Any product change will be announced by PCN.