

DATA SHEET

METAL FILM RESISTORS

High Power, Flameproof
FMP Series

$\pm 1\%$, $\pm 5\%$
1/2W to 3W
RoHS compliant & Halogen Free



YAGEO

Product specification – January 13, 2026 V.9





ORDERING INFORMATION

Part number of the high power, flameproof metal film resistor are identified by the series, power rating, tolerance, packing , temperature coefficient, forming and resistance value.

PART NUMBER

FMP **200** **F** **T** **F** **52-** **100R**
(1) (2) (3) (4) (5) (6) (7)

(1) SERIES

FMP Series

(2) POWER RATING

$$\begin{array}{ll} -50 = 1/2W & 3WS = 3W \\ 100 = 1W & 300 = 3W \\ 200 = 2W & \end{array}$$

(3) TOLERANCE

$$F = \pm 1\% \qquad \qquad \qquad J = \pm 5\%$$

(4) PACKAGING

(5) TEMPERATURE COEFFICIENT OF RESISTANCE

E = $\pm 50\text{ppm}/^\circ\text{C}$ - = Based on spec.
F = $\pm 100\text{ppm}/^\circ\text{C}$

(6) FORMING

26- = 26mm	M = M Type Forming
52- = 52.4mm	F = F Type Forming
73- = 73mm	FK = FK Type Forming
52E = 52.4mm, $\Phi d=0.70\pm0.05\text{mm}$	FFK = FFK Type Forming
52J = 52.4mm, $\Phi d=0.8\pm0.05\text{mm}$	FKK = FKK Type Forming
52G = 52.4mm, $\Phi d\geq0.6\text{mm}$	FT = FT Type Forming
52N = 52.4mm without lacquer on soldering spots and $\Phi d=0.6\pm0.02\text{mm}$	MT = MTsert PN = PANAsert AV = AVsert

Note:26mm, 52.4mm and 73mm represent dimension A of the axial type, please refer to the category of AXIAL/REEL TAPE SPECIFICATION for the detail.

(7) RESISTANCE VALUE


E24 & E96 Series

Example:


$$100R = 100\Omega, 10K = 10,000\Omega, 1M = 1,000,000\Omega$$

DIMENSIONS

Unit: mm



Ultra Miniature	L	ΨD	H	Ψd
FMP-50	3.4 ± 0.3	1.9 ± 0.2	28 ± 2.0	0.45 ± 0.05
FMP100	6.3 ± 0.5	2.4 ± 0.2	28 ± 2.0	0.55 ± 0.05
FMP200	9.0 ± 0.5	3.9 ± 0.3	26 ± 2.0	0.55 ± 0.05
FMP3WS	11.5 ± 1.0	4.5 ± 0.5	35 ± 2.0	0.8 ± 0.05
FMP300	15.5 ± 1.0	5.0 ± 0.5	33 ± 2.0	0.8 ± 0.05

DERATING CURVE**ELECTRICAL CHARACTERISTICS**

CHARACTERISTICS	FMP-50	FMP100	FMP200	FMP3WS	FMP300
Power Rating at 70 °C	1/2W	1W	2W	3W	3W
Maximum Working Voltage	200V	350V	500V	500V	750V
Maximum Overload Voltage	400V	600V	700V	700V	1000V
Voltage Proof on Insulation	300V	500V	500V	500V	500V
Resistance Range	1Ω ~ 4M7Ω for E24 & E96 series value				
Operating Temp. Range	- 55°C to +155°C				
Temperature Coefficient	$\pm 100\text{ppm}/^\circ\text{C}$, $\pm 50\text{ppm}/^\circ\text{C}$ (FMP-50 & FMP100 types, $R \geq 10\text{R}\Omega$)				

Note: For resistance value out of above range is by request.

TEST AND REQUIREMENTS

TEST	TEST METHOD	PROCEDURE	APPRAISE
Short Time Overload	IEC 60115-1 4.13	2.5 times RCWV for 5 sec.(Not more than maximum overload voltage)	$\pm 1.0 \% + 0.05\Omega$
Voltage Proof on Insulation	IEC 60115-1 4.7	In V-Block for 60 sec. test voltage as above table	No Breakdown
Temperature Coefficient	IEC 60115-1 4.8	Between -55°C to +155°C	By Type
Insulation Resistance	IEC 60115-1 4.6	In V-Block for 60 sec.	$>1,000M\Omega$
Solderability	IEC 60115-1 4.17	$245\pm 5^{\circ}\text{C}$ for 3 ± 0.5 Sec.	95% Min. coverage
Solvent Resistance of Marking	IEC 60115-1 4.30	IPA for 5 ± 0.5 Min. with ultrasonic	No deterioration of coatings and markings
Robustness of Terminations	IEC 60115-1 4.16	Direct load for 10 Sec. in the direction of the terminal leads	$\geq 2.5\text{Kg}(24.5\text{N})$
Periodic-pulse Overload	IEC 60115-1 4.39	4 times RCWV(or Umax., whichever less) 10,000 cycles (1 Sec. on, 25 Sec.off)	$\pm 1.0\%+0.05\Omega$
Damp Heat Steady State	IEC 60115-1 4.24	$40\pm 2^{\circ}\text{C}$, 90-95% RH for 56 days, loaded with 0.1 times RCWV(or Umax., whichever less)	$\pm 2.0\%+0.05\Omega$
Endurance at 70°C	IEC 60115-1 4.25	$70\pm 2^{\circ}\text{C}$ at RCWV(or Umax., whichever less) for 1,000 Hr.(1.5 Hr.on,0.5 Hr. off)	$\pm 2.0\%+0.05\Omega$
Temperature Cycling	IEC 60115-1 4.19	$-55^{\circ}\text{C} \rightarrow$ Room Temp. $\rightarrow +155^{\circ}\text{C}$ \rightarrow Room Temp.(5 cycles)	$\pm 1.0\%+0.05\Omega$
Resistance to Soldering Heat	IEC 60115-1 4.18	$260\pm 3^{\circ}\text{C}$ for 10 ± 1 Sec., immersed to a point $3\pm 0.5\text{mm}$ from the body	$\pm 0.25\%+0.05\Omega$
Accidental Overload Test	IEC 60115-1 4.26	4 times RCWV(or Umax., whichever less) for 1 Min.	No evidence of flaming or arcing

Note:

RCWV (Rated Continuous Working Voltage):

The DC or AC (rms) continuous working voltage corresponding to the rated power is determined by the following formula:

$$V = \sqrt{P \times R}$$


or max. working voltage whichever is less

Where


V=Continuous rated DC or
AC (rms) working voltage (V)

P=Rated power (W)


R=Resistance value (Ω)

PULSE DIAGRAMS

FMP100 Series: P_{max} : Maximum permissible peak pulse power
ti: Pulse duration
tp: Pulse repetition time




FMP200 Series: P_{max} : Maximum permissible peak pulse power
ti: Pulse duration
tp: Pulse repetition time



FMP300 Series: P_{max} : Maximum permissible peak pulse power


t_i : Pulse duration

tp : Pulse repetition time


AXIAL / REEL TAPE SPECIFICATION

Unit: mm

Ultra Miniature	a	A	B1-B2 (Max.)	S (spacing)	T (max. deviation of spacing)
FMP-50	6 ± 0.5	52.4 ± 1.5	1.2		
		26.0 ± 1.5	1	5	
FMP100 FMP200	6 ± 0.5	52.4 ± 1.5	1.2	5	0.5 mm per 5 spacing 1 mm per 10 spacing
FMP3WS	6 ± 0.5	73.0 ± 1.5	1.5		
		52.4 ± 1.5	1.2	5	
FMP300	6 ± 0.5	73.0 ± 1.5	1.5		
		52.4 ± 1.5	1.2	10	

TAPE ON REEL PACKING


TYPE	Across Flange(A)	B	Quantity Per Reel
FMP-50	66.5	75.5	5,000
FMP100	66.5	75.5	5,000
FMP200	66.5	75.5	2,500
FMP3WS	87	96	2,000
FMP300	87	96	1,000

TAPE ON BOX PACKING

TYPE	DIMENSIONS			Unit: mm/piece
Ultra Miniature	A	B	C	Quantity Per Box
FMP-50	81	70	260	5,000
FMP100	81	104	260	5,000
FMP200	73	45	258	1,000
FMP3WS	103	78	260	1,000
FMP300	103	94	260	1,000
FMP300	81	91	260	1,000


BULK PACKING

Ultra Miniature	Piece/Per Inner Box	Bag/Per Inner Box	Piece Per Bag
FMP-50	10,000	10	1,000
FMP100	10,000	10	1,000
FMP200	5,000	5	1,000
FMP3WS	2,000	4	500
FMP300	1,000	2	500

FORMING**M TYPE**


TYPE	DIMENSIONS					Unit: mm
Ultra Miniature	L	ψD	ψd	P	H	
FMP-50	3.4 ± 0.3	1.9 ± 0.2	0.45 ± 0.05	6.0 ± 1	10.0 ± 1	
FMP100	6.3 ± 0.5	2.4 ± 0.2	0.55 ± 0.05	10.0 ± 1	10.0 ± 1	
FMP300	15.5 ± 1.0	5.0 ± 0.5	0.8 ± 0.05	20.0 ± 1	15.0 ± 1	

MHA TYPE




TYPE	DIMENSIONS							Unit: mm
Miniature	L	ψD	ψd	B	H0	H1	P	P0
	9.0±0.5	3.9±0.3	0.55±0.05	17.5Max	19.0±1.0	4.0±1.0	30.0±1.0	15.0±0.3
FMP200	P1	P2	F	W	W0	W1	ψD0	
	7.5±1.0	3.75±0.5	7.5±0.5	18.0±0.5	5.0Min	9.0±0.5	4.0±0.2	

MHB TYPE



TYPE	DIMENSIONS									Unit: mm
Miniature	L	ψD	ψd	B	H	H0	H1	H2	H3	
	15.5±1.0	5.0±0.5	0.8±0.05	21.0Max.	30Max.	18.0±1.0	5.5(Ref.)	8.0±1.5	16Max.	
FMP300	P	P0	P1	P2	F	W	W0	W1	ψD0	
	30.0±1.0	15.0±0.3	7.5±1.0	3.75±0.8	7.5±0.5	18.0±0.5	5.0Min.	9.0±0.5	4.0±0.3	

MHC TYPE




TYPE	DIMENSIONS								Unit: mm
Miniature	L	ψD	ψd	B	H	H1	P	P0	
	15.5±1.0	5.0±0.5	0.8±0.05	21.0Max.	19.0±1.0	5.25±1.0	30.0±1.0	15.0±0.3	
FMP300	F	W	W0	W1	ψD0				
	10.0±0.5	18.0±0.5	5.0Min.	9.0±0.5	4.0±0.2				

F TYPE

FK TYPE


FFK TYPE

FKK TYPE




TYPE	DIMENSIONS								Unit: mm	
Ultra Miniature	L	ψD	ψd	P	h	H Max.	hl	HI Max.	E Max.	e
FMP200	9.0±0.5	3.9±0.3	0.55±0.05	6±1	8±1	22	5±1	18.5	3.5	3.5±1
FMP300	15.5±1	5.0±0.5	0.8±0.05	8±1	8±1	28	5±1	25	3.5	3.5±1

FT TYPE (Taping Pack)




MT TYPE (Taping Pack)

Rated Watts : 0.5W




TYPE	DIMENSIONS			Unit: mm
Ultra Miniature	H1 Max.	H2 Max.	H3 Max.	
FMP100	10	18.5	8.5	
FMP200	13	21.5	8.5	
FMP3WS	16	24.5	8.5	

PN TYPE (Taping Pack)




AV TYPE (Taping Pack)




TYPE	DIMENSIONS			Unit: mm
Ultra Miniature	H1 Max.	H2 Max.	H3 Max.	
FMP100	13	21.5	8.5	
FMP200	17	25.5	8.5	
FMP3WS	19	27.5	8.5	

TYPE	DIMENSIONS			Unit: mm
Ultra Miniature	H1 Max.	H2 Max.	H3 Max.	
FMP100	11.5	20	8.5	
FMP200	14.5	23	8.5	
FMP3WS	17.5	26	8.5	

MARKING

COLOR	1st BAND	2nd BAND	3rd BAND	MULTIPLIER	TOLERANCE
BLACK	0	0	0	1Ω	
BROWN	1	1	1	10Ω	± 1% (F)
RED	2	2	2	100Ω	
ORANGE	3	3	3	1KΩ	
YELLOW	4	4	4	10KΩ	
GREEN	5	5	5	100K	
BLUE	6	6	6	1MΩ	
VIOLET	7	7	7	10MΩ	
GREY	8	8	8	0.001Ω	
WHITE	9	9	9	0.0001Ω	
GOLD				0.1Ω	± 5 % (J)
SILVER				0.01Ω	



REVISION HISTORY

REVISION	DATE	CHANGE NOTIFICATION	DESCRIPTION
Version 9	Jan.13, 2026		- Added 52N type
Version 8	Dec.10, 2025		- Added 52- type for FMP300
Version 7	Jun.5, 2025		- Added FK&FFK&FKK type for FMP200
Version 6	May.14, 2024		- Added 52G type
Version 5	Apr.2, 2024		- Added forming code description for part number
Version 4	Aug.31, 2023		- Update legal disclaimer and footer version numbers
Version 3	May.25, 2023		- Updated the tape specification of FMP300
Version 2	Oct.25, 2021		- Add F type for FMP200 series
Version 1	Oct.12, 2021	-	- Updated the tape specification of FMP200
Version 0	Aug.2, 2021	-	- First issue of this specification

"Yageo reserves all the rights for revising the content of this datasheet without further notification, as long as the products itself are unchanged. Any product change will be announced by PCN."

LEGAL DISCLAIMER

YAGEO, its distributors and agents (collectively, "YAGEO"), hereby disclaims any and all liabilities for any errors, inaccuracies or incompleteness contained in any product related information, including but not limited to product specifications, datasheets, pictures and/or graphics. YAGEO may make changes, modifications and/or improvements to product related information at any time and without notice.

YAGEO makes no representation, warranty, and/or guarantee about the fitness of its products for any particular purpose or the continuing production of any of its products. To the maximum extent permitted by law, YAGEO disclaims (i) any and all liability arising out of the application or use of any YAGEO product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for a particular purpose, non -infringement and merchantability.

YAGEO products are designed for general purpose applications under normal operation and usage conditions. Please contact YAGEO for the applications listed below which require especially high reliability for the prevention of defects which might directly cause damage to the third party's life, body or property: Aerospace equipment (artificial satellite, rocket, etc.), Atomic energy-related equipment, Aviation equipment, Disaster prevention equipment, crime prevention equipment, Electric heating apparatus, burning equipment, Highly public information network equipment, data-processing equipment, Medical devices, Military equipment, Power generation control equipment, Safety equipment, Traffic signal equipment, Transportation equipment and Undersea equipment, or for any other application or use in which the failure of YAGEO products could result in personal injury or death, or serious property damage. Particularly **YAGEO Corporation and its affiliates do not recommend the use of commercial or automotive grade products for high reliability applications or manned space flight.**

Information provided here is intended to indicate product specifications only. YAGEO reserves all the rights for revising this content without further notification, as long as products are unchanged. Any product change will be announced by PCN.