

RF Inductor

Automotive Grade

AWHP Series



Overview

Wire-wound RF inductors are electronic components designed to store energy in a magnetic field when electrical current passes through them. They are constructed by winding a conductive wire (usually copper or gold-plated) around a core material such as air, ceramic, or ferrite.

This configuration allows them to provide high inductance values with minimal power loss, especially at high frequencies.

Benefits

1. High Q-Factor (Quality Factor)
2. Wide Frequency Range
3. Low Signal Loss
4. High Current Handling
5. Can maintain excellent thermal stability at different temperatures

Applications

1. Automotive Electronics: infotainment systems, ADAS, and car keyless entry systems.
2. Industrial and Medical Equipmen: RFID systems and medical imaging equipment.
3. Data Centers and Networking
4. Consumer Electronics

Product Information

Series	Size Code (JIS/EIA)	Inductance (nH)
AWHP	1005/0402	1 ~ 390
	1608/0603	




AWHP00110706 Series Specification

AEC-Q200

1 Scope: This specification applies to Wire Wound Ceramic Chip Inductors

2 Part Numbering:



3 Rating:

Operating Temperature: - 40 °C ~ 125 °C

(Including self - temperature rise)

Storage Temperature: - 40 °C ~ 125 °C

(The storage temperature range is for after the assembly)

4 Marking:

No Marking


5 Standard Testing Condition

	Unless otherwise specified	In case of doubt
Temperature	Ordinary Temperature(15 to 35°C)	20 to 30°C
Humidity	Ordinary Humidity(25 to 85% RH)	50 to 80 %RH

AWHP00110706 Series Specification

AEC-Q200

6 Configuration and Dimensions and Unit Weight:



Net Weight (grms)

SIZE CODE	Net Weight (grms)
110706	0.0008 (typ.)

7 Electrical Characteristics:

Part No.	Inductance (nH)	L/Q Test Freq. (MHz)	Q Typ.	SRF (MHz)Typ.	RDC (Ω)Max.	I _{rms} (mA)Max.	Tolerance (±%)
AWHP001107061N0□00	1	250/250	18	16000	0.03	2300	0.1nH,2
AWHP001107062N0□00	2	250/250	18	15200	0.038	2100	0.2nH,2
AWHP001107062N2□00	2.2	250/250	25	15100	0.045	2100	0.2nH,2
AWHP001107062N4□00	2.4	250/250	25	14000	0.045	2000	0.2nH,2
AWHP001107062N7□00	2.7	250/250	20	13000	0.09	1500	0.2nH,2
AWHP001107063N3□00	3.3	250/250	20	12800	0.05	1700	2,3,5
AWHP001107063N6□00	3.6	250/250	28	11700	0.065	1700	2,3,5
AWHP001107063N9□00	3.9	250/250	28	9500	0.065	1700	2,3,5
AWHP001107064N3□00	4.3	250/250	22	7150	0.06	1600	2,3,5
AWHP001107064N7□00	4.7	250/250	18	6850	0.115	1500	2,3,5
AWHP001107065N1□00	5.1	250/250	20	6800	0.125	1200	2,3,5
AWHP001107065N6□00	5.6	250/250	28	6800	0.07	1600	2,3,5
AWHP001107066N2□00	6.2	250/250	25	5800	0.07	1600	2,3,5
AWHP001107066N8□00	6.8	250/250	25	5800	0.095	1500	2,3,5
AWHP001107067N5□00	7.5	250/250	25	5400	0.13	1400	2,3,5
AWHP001107068N2□00	8.2	250/250	30	5400	0.08	1500	2,3,5
AWHP001107068N7□00	8.7	250/250	30	5000	0.085	1500	2,3,5
AWHP001107069N0□00	9	250/250	28	5000	0.09	1400	2,3,5
AWHP001107069N5□00	9.5	250/250	30	4700	0.095	1400	2,3,5
AWHP0011070610N□00	10	250/250	30	4700	0.12	1300	2,3,5
AWHP0011070611N□00	11	250/250	30	4700	0.095	1400	2,3,5
AWHP0011070612N□00	12	250/250	25	4400	0.11	1200	2,3,5
AWHP0011070613N□00	13	250/250	30	4200	0.14	870	2,3,5
AWHP0011070615N□00	15	250/250	30	3900	0.13	1100	2,3,5
AWHP0011070616N□00	16	250/250	30	3700	0.15	850	2,3,5

NOTE: □-tolerance B=±0.1nH / C=±0.2nH / H=±3% / J=±5%

1. Operating temperature range - 4 0 °C ~ 1 2 5 °C
2. I_{rms} for a 15°C temperature rise from 25°C ambient.
3. L/Q Test OSC @200mV.
4. Inductance would be correct Chilisins standard piece.
5. weight: 0.8(mg) typ.

AWHP00110706 Series Specification

AEC-Q200

Part No.	Inductance (nH)	L/Q Test Freq. (MHz)	Q Typ.	SRF (MHz)Typ.	RDC (Ω)Max.	Irms (mA)Max.	Tolerance (±%)
AWHP0011070618N□00	18	250/250	30	3550	0.16	900	2,3,5
AWHP0011070619N□00	19	250/250	30	3500	0.175	850	2,3,5
AWHP0011070620N□00	20	250/250	30	3500	0.22	780	2,3,5
AWHP0011070621N□00	21	250/250	30	1700	0.36	450	2,3,5
AWHP0011070622N□00	22	250/250	30	3300	0.21	800	2,3,5
AWHP0011070623N□00	23	250/250	30	3150	0.21	700	2,3,5
AWHP0011070624N□00	24	250/250	30	3150	0.26	700	2,3,5
AWHP0011070625N□00	25	250/250	30	3150	0.31	700	2,3,5
AWHP0011070626N□00	26	250/250	30	3150	0.275	700	2,3,5
AWHP0011070627N□00	27	250/250	30	3200	0.3	450	2,3,5
AWHP0011070630N□00	30	250/250	30	2900	0.35	450	2,3,5
AWHP0011070633N□00	33	250/250	30	2800	0.38	490	2,3,5
AWHP0011070636N□00	36	250/250	30	2800	0.48	480	2,3,5
AWHP0011070637N□00	37	250/250	30	2700	0.49	470	2,3,5
AWHP0011070639N□00	39	250/250	30	2600	0.52	450	2,3,5
AWHP0011070640N□00	40	250/250	30	2600	0.52	450	2,3,5
AWHP0011070643N□00	43	250/250	29	2500	0.72	450	2,3,5
AWHP0011070647N□00	47	250/250	30	2400	0.72	420	2,3,5
AWHP0011070651N□00	51	250/250	30	2300	0.98	360	2,3,5

NOTE: □-tolerance B=±0.1nH / C=±0.2nH / H=±3% / J=±5%


1. Operating temperature range - 4 0 °C ~ 1 2 5 °C
2. Irms for a 15°C temperature rise from 25°C ambient.
3. L/Q Test OSC @200mV.
4. Inductance would be correct Chilisin standard piece.
5. weight: 0.8(mg) typ.

AWHP00110706 Series Specification

AEC-Q200

8 AWHP00110706 Series

8.1 Construction:



8.2 Material List:


NO	PART	MATERIAL
1	WIRE	COPPER 180
2	EPOXY	UV GLUE
3	CORE	CERAMIC
4	TERMINAL	Ag/Ni/Sn

AWHP00110706 Series Specification

AEC-Q200


9 Reliability Of Ceramic Wire Wound Chip Inductor/CERAMIC SERIES

1-1.Environmental Performance

No	Item	Specification	Test Method
1-1-1	Board Flex	The forces applied on the right conditions must not damage the terminal electrode and the ferrite.	Test device shall be soldered on the substrate Substrate Dimension: 100x40x1.6mm Deflection: 2.0mm Keeping Time: 60 sec 
1-1-2	Terminal Strength	The chip must not damage the terminal electrode and the ferrite.	Refer to AEC-Q200-006 Test device shall be soldered on the substrate Force 0.5lbs for 60±1 seconds for 0201 series Force 1lbs for 60±1 seconds for 0402 series Force 2lbs for 60±1 seconds for 0603 series Force 1.8Kg for 60±1 seconds for the other series.
1-1-3	Solderability	The electrodes shall be at least 95% covered with new solder coating.	Pre-heating: 150℃, 1min Solder Composition: Sn/3.0Ag/0.5Cu Solder Temperature: 245±5℃ Immersion Time: 4±1sec
1-1-4	Resistance to Soldering Heat	Appearance:No damage Inductance change shall be within ±10%. Q change:within±30% of initial value	Pre-heating: 150℃, 1min Solder Composition: Sn/Ag3.0/Cu0.5 Solder Temperature: 260±5℃ Immersion Time: 10±1sec
1-1-5	Resistance to Solvents	There must be no change in appearance or obliteration of marking.	Inductors must withstand 6 minutes of alcohol or water.
1-1-6	Mechanical Shock	The forces applied on the right conditions must not damage the terminal electrode and the ferrite.	Pulse shape : Half-sine waveform Impact acceleration : 100 g Pulse duration : 6 ms Number of shocks : 18 shocks (3 shocks for each face) Orientation : Bottom, top, left, right, front and rear faces
1-1-7	Vibration	Appearance:No damage Inductance change shall be within ±10%. Q change:within±30% of initial value	Vibration waveform: Sine waveform Vibration frequency: 10Hz~2000Hz Vibration acceleration: 5g Sweep rate: 0.764386octave/minute Duration of test: 12 cycles each of 3 orientations 20 minutes for each cycle Vibration axes: X, Y & Z

1-2.Mechanical Performance

No	Item	Specification	Test Method
1-2-1	High Temperature Exposure (Storage)	Appearance:No damage (for microscope of CASTOR MZ-420X)Inductance change shall be within ±10%.	Temperature: 125±3℃ Time: 1000hrs Measured after exposure in the room condition for 24hrs
1-2-2	Low Temperature Exposure (Storage)	Q change:within±30% of initial value	Temperature: -40±3℃ Time: 1000hrs Measured after exposure in the room condition for 24hrs
1-2-2	Biased Humidity		Temperature: 85±2℃ Relative Humidity: 85% Time: 1000hrs Measured after exposure in the room condition for 24hrs
1-2-3	Temperature Cycling		Total cycles: 1000 cycles Temperature Cycling Test Conditions : -40 to +125 ℃ Soak Mode Condition : 30 minutes Measured after exposure in the room condition for 24hrs
1-2-4	Operational Life	Appearance:No damage Inductance change shall be within ±10%.	Temperature: 125±2℃ Applied Current : Rated Current Time: 1000± 24 hrs Measured after exposure in the room condition for 24hrs
1-2-5	ESD		Test mode : Contact Discharge Discharge level : ±6KV, Discharge interval : 1 second Polarity of the output voltage : Positive and negative Number of discharge : Discharge +/- for 1 time for the 2 test points. Test Mode : Air Discharge Discharge level : ±12KV, ±16KV, ±25KV Discharge interval : < 5 seconds Polarity of the output voltage : Positive and negative Number of discharge : Discharge +/- for 1 time for the 1~2 test points.



Lead-Free(LF)標準溫度分析範圍

Refer to J-STD-020C

管制項目 Item.	升温區 Ramp-up	預熱區 Pre-heating	迴焊區 Reflow	Peak Temp	冷卻區 Cooling
溫度範圍 Temp.scope	R.T ~ 150°C	150°C ~ 200°C	Above 217°C	260±5°C	Peak Temp.~150°C
標準時間 Time spec.	-	60 ~ 180 sec	60 ~ 150 sec	20 ~ 40 sec	-
實際時間 Time result	-	75 ~ 100 sec	90 ~ 120 sec	20 ~ 35 sec	-

NOTE:

- 1.Re-flow possible times : within 3 times
- 2.Nitrogen adopted is recommends while in re-flow
- 3.Products can only be soldered with reflow


AWHP00110706 Series Specification

AEC-Q200

10 Packaging:

10.1 Packaging -Cover Tape


The force for tearing off cover tape is 10 to 100 grams in the arrow direction.



10.2 Packaging Quantity

TYPE	PCS/REEL
110706	4000

10.3 Reel Dimensions



Dimensions in mm


TYPE	A	B	C	D
110706	178±1	60±0.5	12±0.5	1.5±0.5

AWHP00110706 Series Specification

AEC-Q200


10 Packaging:

10.4 Tape Dimensions in mm



TYPE	A	B	C	D	E	F	G	T	K
110706	8.0	0.80	2	1.20	3.5	1.75	2	0.75	0.62

11 Recommended Land Pattern:



Dimensions in mm

TYPE	H(In/mm)	I(In/mm)	J(In/mm)
110706	0.026/0.66	0.014/0.36	0.020/0.51

12 Note:

- Please make sure that your product has been evaluated and confirmed against your specifications when our product is mounted to your product.
- Do not knock nor drop.
- All the items and parameters in this product specification have been prescribed on the premise that our product is used for the purpose, under the condition and in the environment agreed upon between you and us. You are requested not to use our product deviating from such agreement.
- The storage period is less than 12 months. Be sure to follow the storage conditions (Temperature: 5 to 40°C, Humidity: 10 to 75% RH or less).









If the storage period elapses, the soldering of the terminal electrodes may deteriorate.

- Do not use or store in locations where there are conditions such as gas corrosion (salt, acid, alkali, etc.).
- The moisture sensitivity level (MSL) of products is classified as level 1.

AWHP00110706 Series Specification









AEC-Q200

13 Graph:











AWHP00110706 Series Specification

AEC-Q200











AWHP00110706 Series Specification

AEC-Q200











AWHP00110706 Series Specification

AEC-Q200










AWHP00110706 Series Specification

AEC-Q200










AWHP00110706 Series Specification

AEC-Q200









AWHP00110706 Series Specification

AEC-Q200










AWHP00110706 Series Specification

AEC-Q200











AWHP00110706 Series Specification

AEC-Q200



AWHP00110706 Series Specification

AEC-Q200



AWHP00110706 Series Specification

AEC-Q200

