

Power Inductor



BPCI Series



Overview

Power inductors are passive electronic components used in various circuits to store energy in a magnetic field when electrical current flows through them. They are critical in filtering, energy storage, and noise suppression in power electronic systems. They are designed to handle higher currents and are optimized for minimal power loss and thermal efficiency.

Benefits

1. Ferrite SMD Shielded Type
2. Various package size and wide inductance range

Applications

1. AP Routers, STBs
2. LCD TVs and monitors
3. Game consoles
4. LED lightings
5. DC/DC converters

Product Information


Series	L (mm)	W(mm)	T (mm)	Inductance (μH)
BPCI	7.3	7.3	4.6	0.33 ~ 10000
	12.0	12.0	5.0	
	12.0	12.0	6.0	
	12.0	12.0	8.0	
	12.0	12.0	10.0	



BPCI00121280 Series Specification

1 Scope: This specification applies to the Pb Free high current type SMD inductors

2 Part Numbering:



3 Rating:



Operating Temperature: $-40^{\circ}\text{C} \sim 125^{\circ}\text{C}$ (Including self - temperature rise)

Storage Temperature(on tape & reel): -20°C to $+40^{\circ}\text{C}$; 75% RH max.

4 Standard Testing Condition:

	Unless otherwise specified	In case of doubt
Temperature	Ordinary Temperature(15 to 35°C)	20 to 30°C
Humidity	Ordinary Humidity(25 to 85% RH)	50 to 80 %RH

5 Configuration and Dimensions:



A: 12.0 ± 0.5 mm

B: 12.0 ± 0.5 mm

C: 8.0 Max. mm

Net Weight (grms)

SIZE CODE	Net Weight (grms)
121280	4.19(Typ.)

BPCI00121280 Series Specification

6 Electrical Characteristics:

Part No.	Inductance L(μH)	Test Frequency	Resistance RDC(Ω) Max.	Rated DC Current		Tolerance	Marking
				Isat(A)	Irms(A)		
BPCI001212801R0□A0	1.0	100kHz/0.25V	5.5m	18.00	15.00	T	1R0
BPCI001212802R2□A0	2.2	100kHz/0.25V	6.2m	16.00	13.00	T	2R2
BPCI001212803R3□A0	3.3	100kHz/0.25V	13.5m	13.50	7.50	M,T	3R3
BPCI001212804R5□A0	4.5	100kHz/0.25V	15.8m	11.50	6.80	M,T	4R5
BPCI001212804R7□A0	4.7	100kHz/0.25V	15.8m	11.50	6.80	M,T	4R7
BPCI001212805R6□A0	5.6	100kHz/0.25V	16.8m	10.50	6.70	M,T	5R6
BPCI001212806R5□A0	6.5	100kHz/0.25V	17.6m	9.50	6.60	M,T	6R5
BPCI001212806R8□A0	6.8	100kHz/0.25V	17.6m	9.50	6.60	M,T	6R8
BPCI001212807R6□A0	7.6	100kHz/0.25V	20.0m	9.00	6.00	M,T	7R6
BPCI00121280100□A0	10	100kHz/0.25V	21.6m	7.80	5.40	M,T	100
BPCI00121280120□A0	12	100kHz/0.25V	24.3m	7.30	4.90	M,T	120
BPCI00121280150□A0	15	100kHz/0.25V	27.0m	6.50	4.50	M,T	150
BPCI00121280180□A0	18	100kHz/0.25V	39.2m	6.00	3.90	M,T	180
BPCI00121280220□A0	22	100kHz/0.25V	43.2m	5.30	3.60	M,T	220
BPCI00121280270□A0	27	100kHz/0.25V	53.1m	4.80	3.30	M,T	270
BPCI00121280330□A0	33	100kHz/0.25V	64.8m	4.30	3.00	M,T	330
BPCI00121280390□A0	39	100kHz/0.25V	71.0m	4.10	2.80	M,T	390
BPCI00121280470□A0	47	100kHz/0.25V	0.10	3.80	2.50	M,T	470
BPCI00121280560□A0	56	100kHz/0.25V	0.11	3.40	2.35	M,T	560
BPCI00121280680□A0	68	100kHz/0.25V	0.14	3.10	2.10	M,T	680
BPCI00121280820□A0	82	100kHz/0.25V	0.16	2.70	1.95	M,T	820
BPCI00121280101□A0	100	100kHz/0.25V	0.22	2.50	1.70	M,T	101
BPCI00121280121□A0	120	100kHz/0.25V	0.25	2.30	1.60	M,T	121
BPCI00121280151□A0	150	100kHz/0.25V	0.28	2.00	1.42	M,T	151
BPCI00121280181□A0	180	100kHz/0.25V	0.35	1.90	1.30	M,T	181
BPCI00121280201□A0	200	100kHz/0.25V	0.37	1.80	1.23	M,T	201
BPCI00121280221□A0	220	100kHz/0.25V	0.39	1.70	1.16	M,T	221

NOTE: tolerance M=±20% , T=±30%

1. Isat : Based on inductance change (ΔL/Lo : drop 25% Max.) @ambient temperature 25°C
2. Irms : Based on temperature rise (ΔT : 40°C TYP.)
3. Breakdown voltage : 400Vac Max. (Inductance 680uH~10mH)

BPCI00121280 Series Specification

6 Electrical Characteristics:


Part No.	Inductance L(μH)	Test Frequency	Resistance RDC(Ω) Max.	Rated DC Current		Tolerance	Marking
				Isat(A)	Irms(A)		
BPCI00121280271□A0	270	100kHz/0.25V	0.51	1.60	1.06	M,T	271
BPCI00121280281□A0	280	100kHz/0.25V	0.51	1.60	1.06	M,T	281
BPCI00121280331□A0	330	100kHz/0.25V	0.64	1.40	0.95	M,T	331
BPCI00121280391□A0	390	100kHz/0.25V	0.70	1.30	0.88	M,T	391
BPCI00121280471□A0	470	100kHz/0.25V	0.98	1.10	0.79	M,T	471
BPCI00121280561□A0	560	100kHz/0.25V	1.03	1.05	0.75	M,T	561
BPCI00121280681□A0	680	100kHz/0.25V	1.10	1.00	0.70	M	681
BPCI00121280801□A0	800	100kHz/0.25V	1.29	0.90	0.67	M	801
BPCI00121280821□A0	820	100kHz/0.25V	1.29	0.90	0.67	M	821
BPCI00121280102□A0	1000	100kHz/0.25V	1.53	0.85	0.64	K,M	102
BPCI00121280112□A0	1100	100kHz/0.25V	1.66	0.82	0.62	M	112
BPCI00121280122□A0	1200	100kHz/0.25V	1.80	0.80	0.60	M	122
BPCI00121280132□A0	1300	100kHz/0.25V	1.93	0.76	0.58	M	132
BPCI00121280142□A0	1400	100kHz/0.25V	2.10	0.73	0.56	K,M	142
BPCI00121280152□A0	1500	100kHz/0.25V	2.20	0.70	0.55	M	152
BPCI00121280182□A0	1800	10kHz/0.25V	2.50	0.65	0.50	M	182
BPCI00121280202□A0	2000	10kHz/0.25V	2.70	0.62	0.48	M	202
BPCI00121280222□A0	2200	10kHz/0.25V	2.90	0.59	0.46	M	222
BPCI00121280242□A0	2400	10kHz/0.25V	3.20	0.58	0.45	M	242
BPCI00121280282□A0	2800	10kHz/0.25V	3.60	0.53	0.42	M	282
BPCI00121280332□A0	3300	10kHz/0.25V	4.10	0.48	0.39	M	332
BPCI00121280392□A0	3900	10kHz/0.25V	4.70	0.45	0.37	M	392
BPCI00121280472□A0	4700	10kHz/0.25V	5.30	0.42	0.36	M	472
BPCI00121280622□A0	6200	10kHz/0.25V	7.10	0.33	0.30	K,M	622
BPCI00121280682□A0	6800	10kHz/0.25V	7.20	0.30	0.28	M	682
BPCI00121280103□A0	10000	10kHz/0.25V	14.20	0.15	0.15	M	103

NOTE: tolerance M=±20% , T=±30%

1. Isat : Based on inductance change (ΔL/Lo : drop 25% Max.) @ambient temperature 25℃
2. Irms : Based on temperature rise (ΔT : 40℃ TYP.)
3. Breakdown voltage : 400Vac Max. (Inductance 680uH~10mH)

BPCI00121280 Series Specification

6.1 Construction:



6.2 Material List:


NO.	ITEM	DESCRIPTION & TYPE
1	CORE	FERRITE
2	WIRE	MAGNET WIRE (P180)
3	TERMINAL	Ag/Cu/Ni/Sn

BPCI00121280 Series Specification

ELECTRICAL

TEST ITEM	SPECIFICATION	TEST DETAILS
Temperature characteristics	$\Delta L/L20^{\circ}\text{C} \leq \pm 10\%$ $0 \sim 2000 \text{ ppm}/^{\circ}\text{C}$	The test shall be performed after the sample has stabilized in an ambient temperature of -20 to $+85^{\circ}\text{C}$, and the value calculated based on the value applicable in a normal temperature and normal humidity shall be $\Delta L/L20^{\circ}\text{C} \leq \pm 10\%$.

MECHANICAL

TEST ITEM	SPECIFICATION	TEST DETAILS
Substrate bending	$\Delta L/L_0 \leq \pm 5\%$ There shall be no mechanical damage or electrical damage.	The sample shall be soldered onto the printed circuit board in figure 1 and a load applied until the figure in the arrow direction is made approximately 3mm. (keep time 30 seconds) PCB dimension shall be the page 7/9 F(Pressurization)  PRESSURE ROD figure-1

BPCI00121280 Series Specification

MECHANICAL

TEST ITEM	SPECIFICATION	
Vibration	$\Delta L/L_0 \leq \pm 5\%$ There shall be no mechanical damage.	The sample shall be soldered onto the printed circuit board and when a vibration having an amplitude of 1.52mm and a frequency of from 10 to 55Hz/1 minute repeated should be applied to the 3 directions (X,Y,Z) for 2 hours each. (A total of 6 hours)
Solderability	New solder More than 90%	Flux (rosin, isopropyl alcohol{JIS-K-1522}) shall be coated over the whole of the sample before hard, the sample shall then be preheated for about 2 minutes in a temperature of 130~150°C and after it has been immersed to a depth 0.5mm below for 3±0.2 seconds fully in molten solder M705 with a temperature of 245±5°C. More than 90% of the electrode sections shall be covered with new solder smoothly when the sample is taken out of the solder bath.
Resistance to Soldering heat (reflow soldering)	There shall be no damage or problems.	Temperature profile of reflow soldering The graph shows a temperature profile for reflow soldering. The y-axis is Temperature (°C) with markers at 25, 160, 217, and 260. The x-axis is Time. The profile starts at 25°C, rises through a preheat phase (150-200°C, 60-120 sec), enters a liquidus phase (>217°C, 60-150 sec), reaches a peak soldering temperature of 260°C ± 3°C for 10-30 seconds, and then ramps down at 6°C/sec max. The ramp up is at 3°C/sec max. The specimen shall be passed through the reflow oven with the condition shown in the above profile for 1 time. The specimen shall be stored at standard atmospheric conditions for 1 hour, after which the measurement shall be made.

BPCI00121280 Series Specification


ENVIRONMENT CHARACTERISTICS

TEST ITEM	SPECIFICATION																
High temperature storage	$\Delta L/Lo \leq \pm 5\%$ There shall be no mechanical damage.	The sample shall be left for 96 ± 4 hours in an atmosphere with a temperature of 125°C and a normal humidity. Upon completion of the measurement shall be made after the sample has been left in a normal temperature and normal humidity for 1 hour.															
Low temperature storage	$\Delta L/Lo \leq \pm 5\%$ There shall be no mechanical damage.	The sample shall be left for 96 ± 4 hours in an atmosphere with a temperature of $-40 \pm 3^\circ\text{C}$. Upon completion of the test, the measurement shall be made after the sample has been left in a normal temperature and normal humidity for 1 hour.															
Change of temperature	$\Delta L/Lo \leq \pm 5\%$ There shall be no other damage of problems	The sample shall be subject to 5 continuous cycles, such as shown in the table 2 below and then it shall be subjected to standard atmospheric conditions for 1 hour, after which measurement shall be made. table 2 <table border="1" style="margin: 10px auto; border-collapse: collapse;"> <thead> <tr> <th></th><th>Temperature</th><th>Duration</th></tr> </thead> <tbody> <tr> <td>1</td><td>$-40 \pm 3^\circ\text{C}$ (Thermostat No.1)</td><td>30 min.</td></tr> <tr> <td>2</td><td>Standard atmospheric</td><td>No.1→No.2</td></tr> <tr> <td>3</td><td>$125 \pm 2^\circ\text{C}$ (Thermostat No.2)</td><td>30 min.</td></tr> <tr> <td>4</td><td>Standard atmospheric</td><td>No.2→No.1</td></tr> </tbody> </table>		Temperature	Duration	1	$-40 \pm 3^\circ\text{C}$ (Thermostat No.1)	30 min.	2	Standard atmospheric	No.1→No.2	3	$125 \pm 2^\circ\text{C}$ (Thermostat No.2)	30 min.	4	Standard atmospheric	No.2→No.1
	Temperature	Duration															
1	$-40 \pm 3^\circ\text{C}$ (Thermostat No.1)	30 min.															
2	Standard atmospheric	No.1→No.2															
3	$125 \pm 2^\circ\text{C}$ (Thermostat No.2)	30 min.															
4	Standard atmospheric	No.2→No.1															
Moisture storage	$\Delta L/Lo \leq \pm 5\%$ There shall be no mechanical damage.	The sample shall be left for 96 ± 4 hours in a temperature of $40 \pm 2^\circ\text{C}$ and a humidity(RH) of 90~95%. Upon completion of the test, the measurement shall be made after the sample has been left in a normal temperature and normal humidity more than 1 hour.															
Test conditions : The sample shall be reflow soldered onto the printed circuit board in every test.																	

BPCI00121280 Series Specification

7 Packaging:


7.1 Packaging -Cover Tape



7.2 Packaging Quantity

TYPE	PCS/REEL
BPCI00121280	500


7.3 Reel Dimensions





BPCI00121280 Series Specification

7 Packaging:

7.4 Tape Dimensions in mm




Unreeling
Direction



8 Recommended Land Pattern:

(STANDARD PATTERN) Unit : mm



BPCI00121280 Series Specification

9 Note:

1. Please make sure that your product has been evaluated and confirmed against your specifications when our product is mounted to your product.
2. Do not knock or drop.
3. All the items and parameters in this product specification have been prescribed on the premise that our product is used for the purpose, under the condition and in the environment agreed upon between you and us. You are requested not to use our product deviating from such agreement.
4. Please keep the distance between transformer/coil and other components
(refer to the standard IEC 950)
5. The moisture sensitivity level (MSL) of products is classified as level 1.







BPCI00121280 Series Specification

TYPICAL ELECTRICAL CHARACTERISTICS

INDUCTANCE vs. DC CURRENT

TEMPERATURE vs. DC CURRENT

@100KHz/0.25V Ambient Temperature : @25°C









BPCI00121280 Series Specification

TYPICAL ELECTRICAL CHARACTERISTICS

INDUCTANCE vs. DC CURRENT

TEMPERATURE vs. DC CURRENT

@100KHz/0.25V Ambient Temperature : @25°C









BPCI00121280 Series Specification

TYPICAL ELECTRICAL CHARACTERISTICS

INDUCTANCE vs. DC CURRENT

TEMPERATURE vs. DC CURRENT

@100KHz/0.25V Ambient Temperature : @25°C









BPCI00121280 Series Specification

TYPICAL ELECTRICAL CHARACTERISTICS

INDUCTANCE vs. DC CURRENT

TEMPERATURE vs. DC CURRENT

@100KHz/0.25V Ambient Temperature : @25°C









BPCI00121280 Series Specification

TYPICAL ELECTRICAL CHARACTERISTICS

INDUCTANCE vs. DC CURRENT

TEMPERATURE vs. DC CURRENT

@100KHz/0.25V Ambient Temperature : @25°C









BPCI00121280 Series Specification

TYPICAL ELECTRICAL CHARACTERISTICS

INDUCTANCE vs. DC CURRENT

TEMPERATURE vs. DC CURRENT

@100KHz/0.25V Ambient Temperature : @25°C









BPCI00121280 Series Specification

TYPICAL ELECTRICAL CHARACTERISTICS

INDUCTANCE vs. DC CURRENT

TEMPERATURE vs. DC CURRENT

@100KHz/0.25V Ambient Temperature : @25°C









BPCI00121280 Series Specification

TYPICAL ELECTRICAL CHARACTERISTICS

INDUCTANCE vs. DC CURRENT

TEMPERATURE vs. DC CURRENT

@100KHz/0.25V Ambient Temperature : @25°C









BPCI00121280 Series Specification

TYPICAL ELECTRICAL CHARACTERISTICS

INDUCTANCE vs. DC CURRENT

TEMPERATURE vs. DC CURRENT

@100KHz/0.25V Ambient Temperature : @25°C









BPCI00121280 Series Specification

TYPICAL ELECTRICAL CHARACTERISTICS

INDUCTANCE vs. DC CURRENT

TEMPERATURE vs. DC CURRENT

@100KHz/0.25V Ambient Temperature : @25°C









BPCI00121280 Series Specification

TYPICAL ELECTRICAL CHARACTERISTICS

INDUCTANCE vs. DC CURRENT

TEMPERATURE vs. DC CURRENT

@100KHz/0.25V Ambient Temperature : @25°C









BPCI00121280 Series Specification

TYPICAL ELECTRICAL CHARACTERISTICS

INDUCTANCE vs. DC CURRENT

TEMPERATURE vs. DC CURRENT

@100KHz/0.25V Ambient Temperature : @25°C









BPCI00121280 Series Specification

TYPICAL ELECTRICAL CHARACTERISTICS

INDUCTANCE vs. DC CURRENT

TEMPERATURE vs. DC CURRENT

@100KHz/0.25V Ambient Temperature : @25°C









BPCI00121280 Series Specification

TYPICAL ELECTRICAL CHARACTERISTICS

INDUCTANCE vs. DC CURRENT

TEMPERATURE vs. DC CURRENT

@100KHz/0.25V Ambient Temperature : @25°C









BPCI00121280 Series Specification

TYPICAL ELECTRICAL CHARACTERISTICS

INDUCTANCE vs. DC CURRENT

TEMPERATURE vs. DC CURRENT

@10KHz/0.25V Ambient Temperature : @25°C









BPCI00121280 Series Specification

TYPICAL ELECTRICAL CHARACTERISTICS

INDUCTANCE vs. DC CURRENT

TEMPERATURE vs. DC CURRENT

@10KHz/0.25V Ambient Temperature : @25°C









BPCI00121280 Series Specification

TYPICAL ELECTRICAL CHARACTERISTICS

INDUCTANCE vs. DC CURRENT

TEMPERATURE vs. DC CURRENT

@10KHz/0.25V Ambient Temperature : @25°C



BPCI00121280 Series Specification

TYPICAL ELECTRICAL CHARACTERISTICS

INDUCTANCE vs. DC CURRENT

TEMPERATURE vs. DC CURRENT

@10KHz/0.25V Ambient Temperature : @25°C

