

Power Inductor



BPSC Series



Overview

Power inductors are passive electronic components used in various circuits to store energy in a magnetic field when electrical current flows through them. They are critical in filtering, energy storage, and noise suppression in power electronic systems. They are designed to handle higher currents and are optimized for minimal power loss and thermal efficiency.

Benefits

1. Ferrite SMD Shielded Type
2. No thermal aging

Applications

1. AP Routers, STBs
2. LCD TVs and monitors
3. Game consoles
4. LED lightings
5. DC/DC converters

Product Information


Series	L (mm)	W(mm)	T (mm)	Inductance (μH)
BPSC	3.2	3.2	1.55	0.47 ~ 3300
	3.2	3.2	2.0	
	4.0	4.0	1.2	
	4.0	4.0	1.8	
	4.0	4.0	3.0	
	4.7	4.7	2.0	
	4.7	4.7	3.0	
	4.7	4.7	4.0	
	5.7	5.7	2.0	
	5.7	5.7	3.0	
	6.7	6.7	3.0	
	7.3	7.3	3.4	
	7.0	7.0	4.0	
	7.3	7.3	4.5	
	8.3	8.3	4.5	
	10.3	10.5	3.1	
	10.3	10.5	4	
	10.3	10.5	5.1	
	12.5	12.5	4.5	
	12.5	12.5	6	
	12.5	12.5	8	
	12.0	12.0	10.0	



BPSC00101140 Series Specification

1 Scope: This specification applies to SMD Shielded Power Inductors

2 Part Numbering:




3 Rating:

Operating Temperature: - 40°C ~ + 125°C (Including self temp. rise)

Storage Temperature: - 40°C ~ + 125°C (For after the circuit board is mounted)

Storage Temperature: (on tape & reel): -20°C to +40°C; 75% RH max.

4 Marking:



Ex Marking: 100


Marking color : Black

5 Standard Testing Condition

	Unless otherwise specified	In case of doubt
Temperature	Ordinary Temperature(15 to 35°C)	20 to 30°C
Humidity	Ordinary Humidity(25 to 85% RH)	50 to 80 %RH

BPSC00101140 Series Specification

6 Configuration and Dimensions and Unit Weight:



Dimensions in mm

TYPE	A	B	C	D	E	F	G
101140	10.3Max.	10.5Max.	4 Max.	13.5Max.	7.7	3.0	1.2

Net Weight (grms)

SIZE CODE	Net Weight (grms)
101140	1.5(Typ.)

7 Electrical Characteristics:

Part No.	Inductance (μ H)	Test Freq.	RDC (Ω)Max.	Isat(A) Max(Typ)	Irms (A)Typ.	Tolerance	Marking
BPSC001011401R5□00	1.5	100 kHz, 1 V	0.0088	8.5(10.5)	6.5	T,N	1R5
BPSC001011402R2□00	2.2	100 kHz, 1 V	0.012	8.0(10.5)	6.1	T	2R2
BPSC001011402R5□00	2.5	100 kHz, 1 V	0.012	7.5(9.5)	6.1	T	2R5
BPSC001011403R3□00	3.3	100 kHz, 1 V	0.015	7.0(8.7)	5.5	T	3R3
BPSC001011403R8□00	3.8	100 kHz, 1 V	0.015	6.8(8.5)	5.5	T	3R8
BPSC001011404R7□00	4.7	100 kHz, 1 V	0.02	5.8(7.3)	5.4	M,T	4R7
BPSC001011405R2□00	5.2	100 kHz, 1 V	0.024	5.8(7.3)	5.2	M,T	5R2
BPSC001011405R6□00	5.6	100 kHz, 1 V	0.027	5.0(6.5)	4.5	M,T	5R6
BPSC001011406R8□00	6.8	100 kHz, 1 V	0.031	5.0(6.5)	4.4	M,T	6R8
BPSC001011407R0□00	7	100 kHz, 1 V	0.031	4.8(5.9)	4.4	M,T	7R0
BPSC001011408R2□00	8.2	100 kHz, 1 V	0.036	4.5(5.8)	3.8	M,T	8R2
BPSC00101140100□00	10	100 kHz, 1 V	0.04	4.0(5.0)	3.6	M,T	100
BPSC00101140120□00	12	100 kHz, 1 V	0.046	3.7(4.6)	3.4	M,T	120
BPSC00101140150□00	15	100 kHz, 1 V	0.055	3.4(4.3)	2.8	M,T	150
BPSC00101140180□00	18	100 kHz, 1 V	0.075	2.9(3.6)	2.5	M,T	180
BPSC00101140220□00	22	100 kHz, 1 V	0.08	2.6(3.3)	2.4	M,T	220
BPSC00101140270□00	27	100 kHz, 1 V	0.096	2.4(3.0)	2.2	M,T	270
BPSC00101140330□00	33	100 kHz, 1 V	0.098	2.3(2.9)	2.1	M,T	330
BPSC00101140390□00	39	100 kHz, 1 V	0.12	2.1(2.7)	2	M,T	390
BPSC00101140470□00	47	100 kHz, 1 V	0.144	1.8(2.5)	1.8	M,T	470
BPSC00101140560□00	56	100 kHz, 1 V	0.175	1.6(2.1)	1.6	M,T	560
BPSC00101140680□00	68	100 kHz, 1 V	0.204	1.4(1.9)	1.45	M,T	680
BPSC00101140820□00	82	100 kHz, 1 V	0.25	1.3(1.7)	1.4	M,T	820
BPSC00101140101□00	100	100 kHz, 1 V	0.304	1.0(1.6)	1.25	M,T	101
BPSC00101140151□00	150	100 kHz, 1 V	0.506	0.96(1.3)	0.85	M,T	151

NOTE: □-tolerance M=±20% / T=±30% / N=+40% -20%

1. Operating temperature range - 40 °C ~ 125 °C (Including self - temperature rise)
2. Isat for Inductance drop 35% from its value without current.
3. Irms for a 40 °C temperature rise from 25 °C ambient.


BPSC00101140 Series Specification

Part No.	Inductance (μ H)	Test Freq.	RDC (Ω)Max.	Isat(A) Max(Typ)	Irms (A)Typ.	Tolerance	Marking
BPSC00101140221□00	220	100 kHz, 1 V	0.69	0.8(1.0)	0.73	M,T	221
BPSC00101140331□00	330	100 kHz, 1 V	1.09	0.68(0.86)	0.52	M,T	331
BPSC00101140471□00	470	100 kHz, 1 V	1.6	0.60(0.75)	0.46	M,T	471
BPSC00101140561□00	560	100 kHz, 1 V	1.68	0.5(0.68)	0.45	M,T	561

BPSC00101140 Series Specification

8 BPSC00101140 Series

8.1 Construction:



8.2 Material List:

No	Part	Material
1	CORE	FERRITE
2	WIRE	MAGNET WIRE
3	TERMINAL	TERMINAL COPPER

BPSC00101140 Series Specification

9 Reliability Of Ferrite Wire Wound Power Inductor

1-1.Mechanical Performance


No	Item	Specification	Test Method
1-1-1	Vibration	Appearance: No damage Inductance: within $\pm 10\%$ of initial value	Test device shall be soldered on the substrate Oscillation Frequency: 10 to 55 to 10Hz for 1min Amplitude: 1.5mm Time: 2hrs for each axis (X, Y & Z), total 6hrs
1-1-2	Resistance to Soldering Heat	Appearance: No damage	Pre-heating: 150°C, 1min Solder Composition: Sn/Ag3.0/Cu0.5 Solder Temperature: 260 ± 5 °C Immersion Time: 10 ± 1 sec
1-1-3	Solder ability	The electrodes shall be at least 95% covered with new solder coating	Pre-heating: 150°C, 1min Solder Composition: Sn/Ag3.0/Cu0.5 Solder Temperature: 245 ± 5 °C Immersion Time: 4 ± 1 sec
1-1-4	Resistance to solvent	There must be no change in appearance or obliteration of marking.	Inductors must withstand 6 minutes of alcohol or water.

1-2.Environmental Performance

No	Item	Specification	Test Method															
1-2-1	Temperature Shock	Appearance: No damage Inductance:within±10% of initial value	10 cycles (Air to Air) 1 cycles shall consist of: 30 minutes exposure to −55 °C 30 minutes exposure to 125 °C 15 seconds maximum transition between temperatures															
1-2-2	Temperature Cycle		One cycle: <table><tr><th>Step</th><th>Temperature (°C)</th><th>Time (min)</th></tr><tr><td>1</td><td>-40±3</td><td>30</td></tr><tr><td>2</td><td>25±2</td><td>3</td></tr><tr><td>3</td><td>125±3</td><td>30</td></tr><tr><td>4</td><td>25±2</td><td>3</td></tr></table>	Step	Temperature (°C)	Time (min)	1	-40±3	30	2	25±2	3	3	125±3	30	4	25±2	3
Step	Temperature (°C)		Time (min)															
1	-40±3		30															
2	25±2		3															
3	125±3	30																
4	25±2	3																
1-2-3	Humidity Resistance	Total: 100cycles Measured after exposure in the room condition for 24hrs Temperature: 40±2°C Relative Humidity: 90 ~ 95% Time: 1000hrs Measured after exposure in the room condition for 24hrs																
1-2-4	Heat Life	Temperature: 85±3°C Applied Current: Rated Current Time: 1000hrs Measured after exposure in the room condition for 24hrs																
1-2-5	Cold Resistance	Temperature: -40±3°C Time: 1000hrs Measured after exposure in the room condition for 24hrs																

BPSC00101140 Series Specification

Reflow Soldering Profile



Lead-Free(LF)標準溫度分析範圍

Refer to J-STD-020C


管制項目 Item.	升温區 Ramp-up	預熱區 Pre-heating	迴焊區 Reflow	Peak Temp	冷卻區 Cooling
溫度範圍 Temp.scope	R.T ~ 150°C	150°C ~ 200°C	217°C	260±5°C	Peak Temp.~150°C
標準時間 Time spec.	—	60 ~ 180 sec	60 ~ 150 sec	20 ~ 40 sec	—
實際時間 Time result	—	75 ~ 100 sec	90 ~ 120 sec	20 ~ 35 sec	—

BPSC00101140 Series Specification

10 Packaging:

10.1 Packaging -Cover Tape


The force for tearing off cover tape is 10 to 130 grams in the arrow direction.



10.2 Packaging Quantity

TYPE	PCS/REEL
101140	1000

10.3 Reel Dimensions




Dimensions in mm

TYPE	A	B	C	D
101140	330	100	13	24.4

BPSC00101140 Series Specification

10 Packaging:

10.4 Tape Dimensions in mm



11 Recommended Land Pattern:



Dimensions in mm

TYPE	A	B	C
101140	1.6	7.3	3.2



12 Note:

1. Please make sure that your product has been evaluated and confirmed against your specifications when our product is mounted to your product.
2. Do not knock nor drop.
3. All the items and parameters in this product specification have been prescribed on the premise that our product is used for the purpose, under the condition and in the environment agreed upon between you and us. You are requested not to use our product deviating from such agreement.
4. Please keep the distance between transformer/coil and other components (refer to the standard IEC 950)
5. The moisture sensitivity level (MSL) of products is classified as level 1.



BPSC00101140 Series Specification

13 Graph:



BPSC001011401R5□00





BPSC001011402R2□00



BPSC001011402R5□00





BPSC001011403R3□00





BPSC00101140 Series Specification

13 Graph:



BPSC001011403R8□00





BPSC001011404R7□00



BPSC001011405R2□00





BPSC001011405R6□00





BPSC00101140 Series Specification

13 Graph:



BPSC001011406R8□00





BPSC001011407R0□00



BPSC001011408R2□00





BPSC00101140100□00




BPSC00101140 Series Specification

13 Graph:



BPSC00101140120□00





BPSC00101140150□00



BPSC00101140180□00




BPSC00101140220□00





BPSC00101140 Series Specification

13 Graph:



BPSC00101140270□00





BPSC00101140330□00



BPSC00101140390□00





BPSC00101140470□00





BPSC00101140 Series Specification

13 Graph:



BPSC00101140560□00





BPSC00101140680□00



BPSC00101140820□00





BPSC00101140101□00





BPSC00101140 Series Specification

13 Graph:



BPSC00101140151□00





BPSC00101140221□00



BPSC00101140331□00



BPSC00101140471□00



BPSC00101140 Series Specification

13 Graph:

BPSC00101140561□00

