

# Power Inductor



## BPSD Series



### Overview

Power inductors are passive electronic components used in various circuits to store energy in a magnetic field when electrical current flows through them. They are critical in filtering, energy storage, and noise suppression in power electronic systems.

They are designed to handle higher currents and are optimized for minimal power loss and thermal efficiency.

### Benefits

1. Ferrite SMD Shielded Type
2. Unshielded power inductor
3. Various package size and wide inductance range

### Applications

1. Graphic cards
2. DC/DC converters

### Product Information


Series	L (mm)	W (mm)	T (mm)	Inductance (μH)
BPSD	3.3	3.0	1.5	0.15 ~ 8200
	3.3	3.0	2.1	
	4.5	4.0	3.2	
	5.8	5.2	2.5	
	5.8	5.2	3.0	
	5.8	5.2	4.5	
	7.8	7.0	3.5	
	7.8	7.0	5.0	
	10	9.0	4.0	
	10	9.0	5.4	
	10	9.0	6.5	



# BPSD00100954 Series Specification

**1 | Scope:** This specification applies to SMD Unshielded Power Inductors

## 2 || Part Numbering:




3 || Rating:

Operating Temperature: - 40°C ~ + 125°C (Including self temp. rise)

Storage Temperature: - 40°C ~ + 125°C(For after the circuit board is mounted)

Storage Temperature: (on tape & reel): -20 °C to +40 °C; 75% RH max.

## 4 || Marking:



Ex Marking : 100



Marking color : Black

## 5 || Standard Testing Condition

	Unless otherwise specified	In case of doubt
Temperature	Ordinary Temperature(15 to 35°C)	20 to 30°C
Humidity	Ordinary Humidity(25 to 85% RH)	50 to 80 %RH

## BPSD00100954 Series Specification

### 6 Configuration and Dimensions:



Dimensions in mm	
TYPE	100954
A	10.0±0.4
B	9.0±0.4
C	5.4±0.4
D	2.1

### Net Weight (grms)

SIZE CODE	Net Weight (grms)
100965	1.96(Typ.)

### 7 Electrical Characteristics:

Part No.	Inductance (uH)	Test Freq.	RDC (Ω)Max.	Isat (A)	Irms (A)	Tolerance (±%)	Marking
BPSD001009543R3□00	3.3	7.96 MHz,1 V	0.038	2.8	2.8	20	3R3
BPSD001009544R7□00	4.7	7.96 MHz,1 V	0.04	2.6	2.6	20	4R7
BPSD001009545R6□00	5.6	7.96 MHz,1 V	0.037	4.5	4.5	20	5R6
BPSD001009546R8□00	6.8	7.96 MHz,1 V	0.037	4.33	4.33	20	6R8
BPSD001009548R2□00	8.2	7.96 MHz,1 V	0.05	3.5	3.5	20	8R2
BPSD00100954100□00	10	2.52 MHz,1 V	0.06	2.6	2.6	10,20	100
BPSD00100954120□00	12	2.52 MHz,1 V	0.07	2.45	2.45	20	120
BPSD00100954150□00	15	2.52 MHz,1 V	0.08	2.27	2.27	10,20	150
BPSD00100954180□00	18	2.52 MHz,1 V	0.09	2.15	2.15	20	180
BPSD00100954220□00	22	2.52 MHz,1 V	0.1	1.95	1.95	10,20	220
BPSD00100954270□00	27	2.52 MHz,1 V	0.11	1.76	1.76	10,20	270
BPSD00100954330□00	33	2.52 MHz,1 V	0.12	1.5	1.5	10,20	330
BPSD00100954390□00	39	2.52 MHz,1 V	0.14	1.37	1.37	10,20	390
BPSD00100954470□00	47	2.52 MHz,1 V	0.17	1.28	1.28	10,20	470
BPSD00100954560□00	56	2.52 MHz,1 V	0.19	1.17	1.17	10,20	560
BPSD00100954680□00	68	2.52 MHz,1 V	0.22	1.11	1.11	10,20	680
BPSD00100954820□00	82	2.52 MHz,1 V	0.25	1	1	10,20	820
BPSD00100954101□00	100	1 kHz,1 V	0.35	0.97	0.97	10,20	101
BPSD00100954121□00	120	1 kHz,1 V	0.4	0.89	0.89	10,20	121
BPSD00100954151□00	150	1 kHz,1 V	0.47	0.78	0.78	10,20	151
BPSD00100954181□00	180	1 kHz,1 V	0.63	0.72	0.72	10,20	181
BPSD00100954221□00	220	1 kHz,1 V	0.73	0.66	0.66	10,20	221
BPSD00100954271□00	270	1 kHz,1 V	0.97	0.57	0.57	10,20	271
BPSD00100954331□00	330	1 kHz,1 V	1.15	0.52	0.52	10,20	331
BPSD00100954391□00	390	1 kHz,1 V	1.3	0.48	0.48	10,20	391

NOTE: □-tolerance K=±10% / M=±20%

1.Operating temperature range - 40 °C ~ 125 °C (Including self - temperature rise)

2.Isat for Inductance drop 10% from its value without current.

3.Irms for a 40°C temperature rise from 25°C ambient.


## BPSD00100954 Series Specification

Part No.	Inductance (uH)	Test Freq.	RDC (Ω)Max.	Isat (A)	Irms (A)	Tolerance (±%)	Marking
BPSD00100954471□00	470	1 kHz, 1 V	1.48	0.42	0.42	10,20	471
BPSD00100954561□00	560	1 kHz, 1 V	1.9	0.33	0.33	10,20	561
BPSD00100954681□00	680	1 kHz, 1 V	2.25	0.28	0.28	10,20	681
BPSD00100954821□00	820	1 kHz, 1 V	2.55	0.24	0.24	10,20	821
BPSD00100954102□00	1000	1 kHz, 1 V	3.1	0.2	0.2	10,20	102

## BPSD00100954 Series Specification

### 8 | BPSD00100954 Series

#### 8.1 Construction:



#### 8.2 Material List:

No	Part	Material
1	CORE	FERRITE
2	WIRE	MAGNET WIRE
3	TERMINAL	Ag/Ni/Sn

## BPSD00100954 Series Specification

### 9 Reliability Of Ferrite Wire Wound Power Inductor

#### 1-1.Mechanical Performance


No	Item	Specification	Test Method
1-1-1	Vibration	Appearance: No damage Inductance:within±10% of initial value	Test device shall be soldered on the substrate Oscillation Frequency: 10 to 55 to 10Hz for 1min Amplitude: 1.5mm Time: 2hrs for each axis (X, Y & Z), total 6hrs
1-1-2	Resistance to Soldering Heat	Appearance: No damage	Pre-heating: 150°C, 1min Solder Composition: Sn/Ag3.0/Cu0.5 Solder Temperature: 260±5°C Immersion Time: 10±1sec
1-1-3	Solder ability	The electrodes shall be at least 95% covered with new solder coating	Pre-heating: 150°C, 1min Solder Composition: Sn/Ag3.0/Cu0.5 Solder Temperature: 245±5°C Immersion Time: 4±1sec
1-1-4	Resistance to solvent	There must be no change in appearance or obliteration of marking.	Inductors must withstand 6 minutes of alcohol or water.

#### 1-2.Environmental Performance

No	Item	Specification	Test Method															
1-2-1	Temperature Shock	Appearance: No damage Inductance:within±10% of initial value	10 cycles (Air to Air) 1 cycles shall consist of: 30 minutes exposure to -55 °C 30 minutes exposure to 125 °C 15 seconds maximum transition between temperatures															
1-2-2	Temperature Cycle		One cycle: <table border="1"> <thead> <tr> <th>Step</th> <th>Temperature (°C)</th> <th>Time (min)</th> </tr> </thead> <tbody> <tr> <td>1</td> <td>-40±3</td> <td>30</td> </tr> <tr> <td>2</td> <td>25±2</td> <td>3</td> </tr> <tr> <td>3</td> <td>125±3</td> <td>30</td> </tr> <tr> <td>4</td> <td>25±2</td> <td>3</td> </tr> </tbody> </table> Total: 100cycles Measured after exposure in the room condition for 24hrs	Step	Temperature (°C)	Time (min)	1	-40±3	30	2	25±2	3	3	125±3	30	4	25±2	3
Step	Temperature (°C)	Time (min)																
1	-40±3	30																
2	25±2	3																
3	125±3	30																
4	25±2	3																
1-2-3	Humidity Resistance		Temperature: 40±2°C Relative Humidity: 90 ~ 95% Time: 1000hrs Measured after exposure in the room condition for 24hrs															
1-2-4	Heat Life		Temperature: 85±3°C Applied Current: Rated Current Time: 1000hrs Measured after exposure in the room condition for 24hrs															
1-2-5	Cold Resistance		Temperature: -40±3°C Time: 1000hrs Measured after exposure in the room condition for 24hrs															

## BPSD00100954 Series Specification

### Reflow Soldering Profile



Lead-Free(LF)標準溫度分析範圍

Refer to J-STD-020C


管制項目 Item.	升溫區 Ramp-up	預熱區 Pre-heating	迴焊區 Reflow	Peak Temp	冷卻區 Cooling
溫度範圍 Temp.scope	R.T ~ 150°C	150°C ~ 200°C	217°C	260±5°C	Peak Temp.~150°C
標準時間 Time spec.	-	60 ~ 180 sec	60 ~ 150 sec	20 ~ 40 sec	-
實際時間 Time result	-	75 ~ 100 sec	90 ~ 120 sec	20 ~ 35 sec	-

## BPSD00100954 Series Specification

### 10 | Packaging:

#### 10.1 Packaging -Cover Tape


The force for tearing off cover tape is 10 to 130 grams in the arrow direction.



#### 10.2 Packaging Quantity

TYPE	PCS/REEL
100954	700

#### 10.3 Reel Dimensions




Dimensions in mm

TYPE	A	B	C	D
100954	330	100	13	24.4

## BPSD00100954 Series Specification


### 10|Packaging:

#### 10.4 Tape Dimensions in mm



TYPE	K0	D	E	W	P	P0	P2
100954	5.80	1.55	1.75	24	12	4	2

### 11|Recommended Land Pattern:



Dimensions in mm

TYPE	A	B
100954	11	2.1


### 12|Note:

1. Please make sure that your product has been evaluated and confirmed against your specifications when our product is mounted to your product.
2. Do not knock nor drop.
3. All the items and parameters in this product specification have been prescribed on the premise that our product is used for the purpose, under the condition and in the environment agreed upon between you and us. You are requested not to use our product deviating from such agreement.
4. Please keep the distance between transformer/coil and other components (refer to the standard IEC 950)
5. The moisture sensitivity level (MSL) of products is classified as level 1.


## BPSD00100954 Series Specification

### 13 Graph:


BPSD001009543R3□00








BPSD001009544R7□00



BPSD001009545R6□00




BPSD001009546R8□00




## BPSD00100954 Series Specification

### 13 Graph:


BPSD001009548R2□00








BPSD00100954100□00



BPSD00100954120□00





BPSD00100954150□00





## BPSD00100954 Series Specification

### 13 Graph:


BPSD00100954180□00





BPSD00100954220□00



BPSD00100954270□00




BPSD00100954330□00




## BPSD00100954 Series Specification

### 13 Graph:


BPSD00100954390□00








BPSD00100954470□00



BPSD00100954560□00





BPSD00100954680□00





## BPSD00100954 Series Specification

### 13 Graph:



BPSD00100954820□00





BPSD00100954101□00



BPSD00100954121□00




BPSD00100954151□00




## BPSD00100954 Series Specification

### 13 Graph:


BPSD00100954181□00








BPSD00100954221□00



BPSD00100954271□00





BPSD00100954331□00





## BPSD00100954 Series Specification

### 13 Graph:



BPSD00100954391□00





BPSD00100954471□00



BPSD00100954561□00





BPSD00100954681□00



## BPSD00100954 Series Specification

### 13 Graph:

BPSD00100954821□00



BPSD00100954102□00

